





| Rev | AWO # | Description | Date     | Appr |
|-----|-------|-------------|----------|------|
| -   |       | RELEASED    | 10/24/11 |      |

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

4~15 Circuits



Positions: 2 thru 15  
A = .079 [2.00] x No. of Spaces  
B = .079 [2.00] x No. of Spaces + .110 [2.80]  
C = .079 [2.00] x No. of Spaces + .157 [4.00]

# SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amp max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

.079 [2.00] CRIMP HOUSING

TITLE

APPROVALS

DATE

DRAWN AY 10/24/11

CHECKED

APPROVED

SIZE PART NO. 2CH-D-XX

REV. -

REF: S00123T SCALE: NTS SHEET 1 OF 1

1

2

3

4

5

6