




Part Number : [22112162](#)
Product Description : KK 254 Solid Header, Vertical, with Friction Lock, 16 Circuits, Gold (Au) Plating
Series Number : 6373
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Number : A-6373-16A241



Documents & Resources

Drawings

[022112162_sd.pdf](#)
[PK-6373-001-000.pdf](#)

3D Models and Design Files

[022112162_stp.zip](#)
[SYM-22-23-2161-001.zip](#)

Specifications

[PS-10-07-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	6373
Description	KK 254 Solid Header, Vertical, with Friction Lock, 16 Circuits, Gold (Au) Plating
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	800753592094

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Natural (White)
Durability (mating cycles max)	50

First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	Nylon
Net Weight	1.833/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PC Tail Length	3.56mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

KK 254 Single Row Crimp Housings	<u>2695</u>
KK 254 PC Board Connector	<u>4455</u>
KK 254 Receptacle Housings	<u>7880</u>

This document was generated on Apr 05, 2025