
# 60635-1 ✔ ACTIVE

FASTON | FASTON 250

TE Internal #: 60635-1

TE Internal Description: 250 FASTON REC 14-10 AWG TPBR

View on TE.com >







## Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2025 (250)<br>Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


## Compatible Parts



Downloaded from Arrow.com.



TE Part # 2376595-2
250 FASTON PCB TAB TPBR




TE Part # 7-2150056-7
OCEAN_2.0_SPARE_PART_KIT-140F310F




TE Part # 2150056-2
OCEAN_2.0_APPLICATOR-E-140F310F-REA

## Also in the Series | FASTON 250



Compression Connectors(4)




Crimp Terminal Housings(117)



Insertion & Extraction Tools(6)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(131)



Quick Disconnects(411)



Splices(4)


## Customers Also Bought



TE Part #E24938-000
HX-SCE-1K-12.7-50-S1-9



TE Part #41274
250 FASTON,REC.,18-14 AWG,TPBR




TE Part #63522-1
250 FASTON TAB 20-15 AWG NPST




TE Part #63931-1
187 FASTON REC 22-18 AWG TPBR




TE Part #2-323144-1
TERMINAL,SOLIS SPD FLG 12-10



TE Part #1-480416-1
FASTON 250 REC HSG 1CIR NYLON BLK



TE Part #4-520447-2
ULTRA-FAST 250 ASY REC 12-10 AWG TPBR




TE Part #3-521013-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR



Downloaded from Arrow.com.



TE Part #1742539-3
CLUSTER BLOCK RECEPT,TPCuFeP

TE Part #KMAH1-11-1-C-S1-HE
KMAH1-11-1-C-S1-HE

# Documents

## Product Drawings

250 FASTON REC 14-10 AWG TPBR

English

## CAD Files

### Customer View Model

ENG_CVM_CVM_60635-1_AL.2d_dxf.zip

English

3D PDF

3D

### Customer View Model

ENG_CVM_CVM_60635-1_AL.3d_igs.zip

English

### Customer View Model

ENG_CVM_CVM_60635-1_AL.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

## Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

FASTON TERMINALS (INSULATED AND UNINSULATED) - FULL CATALOG

English

## Product Specifications

Engineering Report

English

## Agency Approvals

UL Report

English



Downloaded from Arrow.com.