





REV.	DATE	DESCRIPTION
NC	05/05/97	INITIAL RELEASE
A	01/11/07	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .118"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	01/11/07							PART DESCRIPTION TNC REVERSE POLARITY CRIMP JACK (FOR BELDEN 9913, 9914)				
7						CHECKED													
6						ISSUED													
5						SHEET		1 OF 1		PART NO. 122392RP									
4	FERRULE	COPPER	NICKEL	1															
3	CONTACT PIN	BRASS	GOLD	1		CAD FILE				DWG. NO.		122392RP.DWG	REV. A	SIZE A	SCALE NA				
2	INSULATOR	TEFLON	NATURAL	1		C:/122/122392RP.DWG													
1	BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															