



Part Number : [1461531150](#)

Product Description : Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 150.00mm Cable Length, Compatible with I-PEX MHF4 Connectors

Series Number : 146153

Status : Active

Product Category : Antennas



Documents and Resources

Drawings

[1461531150_sd.pdf](#)

[1461530100-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[AS-146153-100-001.pdf](#)

[PS-146153-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	146153
Description	Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 150.00mm Cable Length, Compatible with I-PEX MHF4 Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	2.4/5GHz Balanced Flex Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Internal, Wi-Fi Antenna
UPC	191128463256

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5930
Band#2 F_Start (MHz)	4900
Electrical Connectivity	Cable

Peak Gain (dBi)	2.8 @ 2.4 GHz, 3.7 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>70% @ 5 GHz, >72% @2.4 GHz

Physical

Cable Length	150.00mm
Length	34.90mm
Mounting Style	Adhesive
Net Weight	0.682/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	9.00mm

This document was generated on May 20, 2026