

# CMH04

Unit: mm

## Switching Mode Power Supply Applications


- Repetitive peak reverse voltage:  $V_{RRM} = 200\text{ V}$
- Average forward current:  $I_F (AV) = 1\text{ A}$
- Low forward voltage:  $V_{FM} = 0.98\text{ V (Max)} @ I_{FM} = 1\text{ A}$
- Very Fast Reverse-Recovery Time:  $t_{rr} = 35\text{ ns (Max)}$
- Suitable for compact assembly due to small surface-mount package  
"M-FLAT™" (Toshiba package name)

## Absolute Maximum Ratings ( $T_a = 25^\circ\text{C}$ )

| Characteristics                                       | Symbol     | Rating     | Unit             |
|-------------------------------------------------------|------------|------------|------------------|
| Repetitive peak reverse voltage                       | $V_{RRM}$  | 200        | V                |
| Average forward current                               | $I_F (AV)$ | 1 (Note 1) | A                |
| Peak one cycle surge forward current (non-repetitive) | $I_{FSM}$  | 20 (50 Hz) | A                |
| Junction temperature                                  | $T_j$      | -40 to 150 | $^\circ\text{C}$ |
| Storage temperature range                             | $T_{stg}$  | -40 to 150 | $^\circ\text{C}$ |

Note 1:  $T_a = 26^\circ\text{C}$  Device mounted on a glass-epoxy board  
board size: 50 mm × 50 mm  
soldering land: 6 mm × 6 mm  
glass-epoxy board thickness: 1.6 mm

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings. Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc.).



Weight: 0.023 g (typ.)

## Electrical Characteristics ( $T_a = 25^\circ\text{C}$ )


| Characteristics                          | Symbol         | Test Condition                                                                                                                | Min | Typ. | Max  | Unit                      |
|------------------------------------------|----------------|-------------------------------------------------------------------------------------------------------------------------------|-----|------|------|---------------------------|
| Peak forward voltage                     | $V_{FM} (1)$   | $I_{FM} = 0.1\text{ A (pulse test)}$                                                                                          | —   | 0.70 | —    | V                         |
|                                          | $V_{FM} (2)$   | $I_{FM} = 0.7\text{ A (pulse test)}$                                                                                          | —   | 0.84 | —    |                           |
|                                          | $V_{FM} (3)$   | $I_{FM} = 1\text{ A (pulse test)}$                                                                                            | —   | 0.87 | 0.98 |                           |
| Peak repetitive reverse current          | $I_{RRM}$      | $V_{RRM} = 200\text{ V (pulse test)}$                                                                                         | —   | —    | 10   | $\mu\text{A}$             |
| Reverse recovery time                    | $t_{rr}$       | $I_F = 1\text{ A}$ , $di/dt = -30\text{ A}/\mu\text{s}$                                                                       | —   | —    | 35   | ns                        |
| Forward recovery time                    | $t_{fr}$       | $I_F = 1\text{ A}$                                                                                                            | —   | —    | 100  | ns                        |
| Thermal resistance (junction to ambient) | $R_{th} (j-a)$ | Device mounted on a ceramic board (board size: 50 mm × 50 mm) (soldering land: 2 mm × 2 mm) (board thickness: 0.64 mm)        | —   | —    | 60   | $^\circ\text{C}/\text{W}$ |
|                                          |                | Device mounted on a glass-epoxy board (board size: 50 mm × 50 mm) (soldering land: 6 mm × 6 mm) (board thickness: 1.6 mm)     | —   | —    | 135  |                           |
|                                          |                | Device mounted on a glass-epoxy board (board size: 50 mm × 50 mm) (soldering land: 2.1 mm × 1.4 mm) (board thickness: 1.6 mm) | —   | —    | 210  |                           |
| Thermal resistance (junction to lead)    | $R_{th} (j-l)$ | —                                                                                                                             | —   | —    | 16   | $^\circ\text{C}/\text{W}$ |

Start of commercial production  
2002-12

## Marking

| Abbreviation Code | Part No. |
|-------------------|----------|
| H4                | CMH04    |

## Land pattern dimensions for reference only



## Handling Precaution

The absolute maximum ratings denote the absolute maximum ratings, which are rated values and must not be exceeded during operation, even for an instant. The following are the general derating methods that we recommend when you design a circuit with a device.

**V<sub>RRM</sub>:** We recommend that the worst case voltage, including surge voltage, be no greater than 80% of the absolute maximum rating of V<sub>RRM</sub> for a DC circuit and be no greater than 50% of that of V<sub>RRM</sub> for an AC circuit. V<sub>RRM</sub> has a temperature coefficient of 0.1%/°C. Take this temperature coefficient into account designing a device at low temperature.







**I<sub>F(AV)</sub>:** We recommend that the worst case current be no greater than 80% of the absolute maximum rating of I<sub>F(AV)</sub>. Carry out adequate heat design. If you can't design a circuit with excellent heat radiation, set the margin by using an allowable T<sub>amax</sub>-I<sub>F(AV)</sub> curve.


This rating specifies the non-repetitive peak current in one cycle of a 50-Hz sine wave, condition angle 180. Therefore, this is only applied for an abnormal operation, which seldom occurs during the lifespan of the device.

We recommend that a device be used at a T<sub>j</sub> of below 120°C under the worst load and heat radiation conditions.

Thermal resistance between junction and ambient fluctuates depending on the device's mounting condition. When using a device, design a circuit board and a soldering land size to match the appropriate thermal resistance value.

Please refer to the Rectifiers databook for further information.





## RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, Class 3 medical devices, equipment used for automobiles, and military vehicles and munitions. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative or contact us via our website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**