


P-Channel 20 V (D-S) MOSFET

PRODUCT SUMMARY			
V_{DS} (V)	$R_{DS(on)}$ (Ω) Max.	I_D (A)	Q_g (Typ.)
- 20	0.0036 at $V_{GS} = - 10$ V	- 40 ^e	72 nC
	0.0048 at $V_{GS} = - 4.5$ V	- 40 ^e	
	0.0085 at $V_{GS} = - 2.5$ V	- 40 ^e	

FEATURES


- TrenchFET® Power MOSFET
- Low Thermal Resistance PowerPAK® Package with Small Size and Low 0.75 mm Profile
- 100 % R_g and UIS Tested
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



Ordering Information:
Si7655DN-T1-GE3 (Lead (Pb)-free and Halogen-free)

APPLICATIONS

- Smart Phones, Tablet PCs, Mobile Computing
 - Battery Switch
 - Load Switch



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)			
Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	- 20	V
Gate-Source Voltage	V_{GS}	± 12	
Continuous Drain Current ($T_J = 150$ °C)	I_D	- 40 ^e	A
		- 40 ^e	
		- 31 ^{a, b}	
		- 25 ^{a, b}	
Pulsed Drain Current ($t = 300$ μ s)	I_{DM}	- 100	A
Continuous Source-Drain Diode Current	I_S	- 40 ^e	
		- 4 ^{a, b}	
Avalanche Current	I_{AS}	- 20	
Single-Pulse Avalanche Energy	E_{AS}	20	mJ
Maximum Power Dissipation	P_D	57	W
		36	
		4.8 ^{a, b}	
		3 ^{a, b}	
Operating Junction and Storage Temperature Range	T_J, T_{stg}	- 50 to 150	°C
Soldering Recommendations (Peak Temperature) ^{c, d}		260	

Notes:

- Surface mounted on 1" x 1" FR4 board.
- $t = 10$ s.
- See solder profile (www.vishay.com/doc?73257). The PowerPAK 1212-8S is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.
- Rework conditions: manual soldering with a soldering iron is not recommended for leadless components.
- Package limited.

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^{a, b}	R_{thJA}	21	26	°C/W
Maximum Junction-to-Case (Drain)	R_{thJC}	1.7	2.2	

Notes:

a. Surface mounted on 1" x 1" FR4 board.
 b. Maximum under steady state conditions is 63 °C/W.

SPECIFICATIONS ($T_J = 25$ °C, unless otherwise noted)


Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V_{DS}	$V_{GS} = 0$ V, $I_D = -250$ μA	-20			V	
V_{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	$I_D = -250$ μA		-12		mV/ °C	
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$			2.6			
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = -250$ μA	-0.5		-1.1	V	
Gate-Source Leakage	I_{GSS}	$V_{DS} = 0$ V, $V_{GS} = \pm 12$ V			±100	nA	
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = -20$ V, $V_{GS} = 0$ V		-1		μA	
		$V_{DS} = -20$ V, $V_{GS} = 0$ V, $T_J = 55$ °C			-10		
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} \leq -5$ V, $V_{GS} = -10$ V	-20			A	
Drain-Source On-State Resistance ^a	$R_{DS(on)}$	$V_{GS} = -10$ V, $I_D = -20$ A		0.0030	0.0036	Ω	
		$V_{GS} = -4.5$ V, $I_D = -15$ A		0.0039	0.0048		
		$V_{GS} = -2.5$ V, $I_D = -10$ A		0.0062	0.0085		
Forward Transconductance ^a	g_{fs}	$V_{DS} = -15$ V, $I_D = -20$ A		90		S	
Dynamic^b							
Input Capacitance	C_{iss}	$V_{DS} = -10$ V, $V_{GS} = 0$ V, $f = 1$ MHz		6600		pF	
Output Capacitance	C_{oss}			890			
Reverse Transfer Capacitance	C_{rss}			930			
Total Gate Charge	Q_g	$V_{DS} = -10$ V, $V_{GS} = -10$ V, $I_D = -20$ A		150	225	nC	
Gate-Source Charge	Q_{gs}	$V_{DS} = -10$ V, $V_{GS} = -4.5$ V, $I_D = -20$ A		72	110		
Gate-Drain Charge	Q_{gd}			12			
Gate Resistance	R_g			19			
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -10$ V, $R_L = 1$ Ω $I_D \geq -10$ A, $V_{GEN} = -4.5$ V, $R_g = 1$ Ω	$f = 1$ MHz	0.5	2.6	5.2	Ω
Rise Time	t_r				45	90	ns
Turn-Off Delay Time	$t_{d(off)}$				45	90	
Fall Time	t_f				100	200	
Turn-On Delay Time	$t_{d(on)}$				35	70	
Rise Time	t_r				13	25	
Turn-Off Delay Time	$t_{d(off)}$	$V_{DD} = -10$ V, $R_L = 1$ Ω $I_D \geq -10$ A, $V_{GEN} = -10$ V, $R_g = 1$ Ω			10	20	ns
Fall Time	t_f				110	220	
					25	50	
Drain-Source Body Diode Characteristics							
Continuous Source-Drain Diode Current	I_S	$T_C = 25$ °C			-40 ^c	A	
Pulse Diode Forward Current ^a	I_{SM}				-100		
Body Diode Voltage	V_{SD}	$I_F = -10$ A		-0.75	-1.2	V	
Body Diode Reverse Recovery Time	t_{rr}	$I_F = -10$ A, $di/dt = 100$ A/μs, $T_J = 25$ °C		30	60	ns	
Body Diode Reverse Recovery Charge	Q_{rr}			17	26	nC	
Reverse Recovery Fall Time	t_a			15		ns	
Reverse Recovery Rise Time	t_b			15			

Notes:


- a. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2 %.
 b. Guaranteed by design, not subject to production testing.
 c. Package limited.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current and Gate Voltage



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature

Si7655DN


Vishay Siliconix

**TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)


Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power, Junction-to-Ambient




Safe Operating Area, Junction-to-Ambient

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Current Derating*




Power, Junction-to-Case

* The power dissipation P_D is based on $T_{J(max)} = 150^\circ\text{C}$, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?63617.

Case Outline for PowerPAK® 1212-8S



DIM.	MILLIMETERS			INCHES								
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.						
A	0.67	0.75	0.83	0.026	0.030	0.033						
A1	0.00	-	0.05	0.000	-	0.002						
A3	0.20 ref.			0.008 ref								
b	0.25	0.30	0.35	0.010	0.012	0.014						
D	3.20	3.30	3.40	0.126	0.130	0.134						
D1	2.15	2.25	2.35	0.085	0.089	0.093						
E	3.20	3.30	3.40	0.126	0.130	0.134						
E1	1.60	1.70	1.80	0.063	0.067	0.071						
e	0.65 bsc.			0.026 bsc.								
K	0.76 ref.			0.030 ref.								
K1	0.41 ref.			0.016 ref.								
L	0.33	0.43	0.53	0.013	0.017	0.021						
Z	0.525 ref.			0.021 ref.								
ECN: C20-0862-Rev. B, 20-Jul-2020												
DWG: 6008												

RECOMMENDED MINIMUM PADS FOR PowerPAK® 1212-8 Single

Recommended Minimum Pads
Dimensions in Inches/(mm)

[Return to Index](#)

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.