


Marking Information



2M4 = Product Type Marking Code
 YM = Date Code Marking
 Y = Year (ex: 1 = 2021)
 M = Month (ex: 3 = March)

Date Code Key

Year	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
Code	H	I	J	K	L	M	N	O	P	R	S	T

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

Absolute Maximum Ratings (@ $T_A = +25^\circ\text{C}$ unless otherwise specified.)

Characteristic	Symbol	Value	Unit
DRAIN BIAS Voltage	$V_{\text{DRAIN-BIAS}}$	40	V
SOURCE DRAIN Voltage	$V_{\text{SOURCE-DRAIN}}$	50	V
BIAS Current	I_{BIAS}	-300	mA
DRAIN Current	I_{DRAIN}	300	mA

Thermal Characteristics – Total Device (@ $T_A = +25^\circ\text{C}$ unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	P_D	300	mW
Thermal Resistance, Junction to Ambient (Note 5)	$R_{\theta JA}$	424	$^\circ\text{C/W}$
Thermal Resistance, Junction to Case (Note 5)	$R_{\theta JC}$	111	$^\circ\text{C/W}$
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +150	$^\circ\text{C}$

Note: 5. For a device mounted on minimum recommended pad layout with 1oz copper that is on a single-sided 1.6mm FR4 PCB; the device is measured under still air conditions whilst operating in a steady-state.

Thermal Characteristics – Total Device




Fig.1 Derating Curve




Fig.2 Safe Operation Area









Fig.3 Transient Thermal Resistance

Electrical Characteristics (@ $T_A = +25^\circ\text{C}$ unless otherwise specified)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
DRAIN - BIAS Voltage	$V_{\text{DRAIN-BIAS}}$	40	78	—	V	$I_{\text{DRAIN}}=100\mu\text{A}$
SOURCE - DRAIN Voltage	$V_{\text{SOURCE-DRAIN}}$	50	84	—	V	$I_{\text{SOURCE}}=100\mu\text{A}$
DRAIN - REF Voltage	$V_{\text{DRAIN-REF}}$	—	588	—	mV	$I_{\text{DRAIN}}=100\mu\text{A}$
SOURCE Current	I_{SOURCE}	—	11.6	—	μA	$V_{\text{SOURCE-REF}}=0.56\text{V}$
REF-SOURCE Voltage	$V_{\text{REF-SOURCE}}$	—	-554	—	mV	$I_{\text{REF}}=-10\mu\text{A}$
Turn-Off Differential Voltage	V_T	5	34	80	mV	$I_{\text{DRAIN}}=100\mu\text{A}; I_{\text{SOURCE}}=10\mu\text{A}$
REF-SOURCE Voltage ($V_{\text{BIAS low}}$)	$V_{\text{REF-SOURCE}}$	-250	-472	—	mV	$V_{\text{BIAS-SOURCE}}=-5\text{V}; I_{\text{BIAS}}=-1\mu\text{A}$
		-300	-541	—	mV	$V_{\text{BIAS-SOURCE}}=-5\text{V}; I_{\text{BIAS}}=-10\mu\text{A}$
REF-SOURCE Voltage ($V_{\text{BIAS high}}$)	$V_{\text{REF-SOURCE}}$	—	-601	-800	mV	$V_{\text{BIAS-SOURCE}}=-0.5\text{V}; I_{\text{BIAS}}=-100\mu\text{A}$
		—	-663	-850	mV	$V_{\text{BIAS-SOURCE}}=-0.5\text{V}; I_{\text{BIAS}}=-1\text{mA}$

Typical Electrical Characteristics (@ $T_A = +25^\circ\text{C}$ unless otherwise specified.)

Fig.4 h_{FE} vs I_C

Fig.5 $V_{CE(sat)}$ vs I_C

Fig.6 $V_{BE(sat)}$ vs I_C

Fig.7 I vs V_F & V_{BE}

Typical Application Circuit/ Pin Out Details/ Functional Description



Typical Application Circuit

Pin	Name	Function
1	NC	No internal connection
2	REF	Reference current to set V_F
3	BIAS	Reference current to set V_{BE} and control Gate
4	SOURCE	V_{OUT} sense voltage
5	NC	No internal connection
6	DRAIN	V_{IN} sense voltage
n/a	Rref	This resistor sets the turn off speed of the FET. The lower the resistance, the more base drive to the transistor, the faster the transistor shorts out the gate to turn off the FET.
n/a	Rbias	This resistor sets the turn on speed of the FET. When the ideal diode circuit is turning on the PNP is held off by the diode and FET voltage drops. It is Rbias that pulls the gate low and turns on the FET.
n/a	Rbias : Rref	Ideal diode Turn-Off threshold voltage $V_T \propto R_{bias} / R_{ref}$
n/a	Vref	Voltage across Rref

Functional Description (Refer to typical application circuit above)

Supply Connect:

As a +Input is applied, the body drain diode of Q1 becomes forward biased. U1 diode holds U1 transistor base at $V_{IN} - V_F$, and so V_{BE} is too low to turn on U1 transistor. As Q1 gate capacitance charges through R_{bias}, Q1 turns on and R_{DS} decreases causing V_{DS} to decrease and V_{BE} to increase until U1 transistor starts to conduct. This process continues until Q1 R_{DS} reaches its minimum value and U1 transistor V_{BE} cannot increase and I_C reaches its maximum. V_{GS} should be high enough at this point to ensure linear operation.

R_{ref} and R_{bias} set the currents through U1 diode and U1 collector respectively so that $V_{F(DIODE)}$ is greater than $V_{BE(on)}$.

Supply Disconnect:

As the +Input is removed, $V_{DS} < V_T$, Q1 is on and $V_{IN} = V_{OUT}$, causing V_{REF} to fall and U1 V_{BE} > V_{BE(on)} so U1 transistor discharges Q1 gate capacitance and Q1 turns off causing V_{IN} to fall to 0V.

Quiescent Current and Isolation:

With a battery connected at Supply Out, there are two leakage paths back to the Supply In. One is straight through Q1 and the other is through U1 emitter-anode. The high reverse breakdown voltage of U1 diode provides a high isolation path. The R_{ref} & R_{bias} currents bias U1 transistor on which keeps Q1 off. These resistors' values are chosen to minimize quiescent current operation of the circuit.



Typical Charging Conditions. (Ta=25°C Vbatt=14V switch closed, Isupply=3A)			
Parameter	Symbol	Typ	Unit
Input Voltage	V _{IN}	14.1	V
Input current	I _{IN}	3	A
Output Voltage	V _{OUT}	14	V
Output Current	I _{OUT}	3.0	A
Diode Forward Voltage	V _F	0.6	V
Diode forward current	I _F	135	uA
Reference Voltage	V _{REF}	13.4	V
Reference Current	I _{REF}	136.6	uA
Base Current	I _B	1.6	uA
Emitter Current	I _E	12.1	uA
Bias Voltage	V _{BIAS}	10.5	V
Collector Current	I _C	10.5	uA
Operating Current	I _{CC}	147	uA

Typical Non-Charging Conditions. (Ta=25°C Vbatt=14V switch open, Isupply=3A)			
Parameter	Symbol	Typ	Unit
Input Voltage	V _{IN}	-	uV
Input current	I _{IN}	--	A
Output Voltage	V _{OUT}	14	V
Output Current	I _{OUT}	--	A
Diode Forward Voltage	V _F	--	V
Diode forward current	I _F	0	uA
Reference Voltage	V _{REF}	13.3	V
Reference Current	I _{REF}	133	uA
Base Current	I _B	133	uA
Emitter Current	I _E	145	uA
Bias Voltage	V _{BIAS}	13.94	V
Bias Current	I _{BIAS}	13.94	uA
Operating Current	I _{CC}	147	uA



Typical Application Circuit/ Pin Out Details/ Functional Description (continued)

Timing

Switching speed is affected by PMOS characteristics, R_{bias} , R_{ref} , and operating voltage. Using the typical application circuit, we can see how modifying values can affect the timing in the simulations below



Typical Application Circuit/ Pin Out Details/ Functional Description (continued)



Ideal Diode Power Saving

Example:

A diode rectifier with a typical forward voltage $V_F = 0.55V$ carrying 3A current would dissipate 1.65W ($I \times V_F$).

Whereas with P-MOSFET such as the DMP4047LFDE that has an $R_{ds(on)}$ of 33m Ω , the power dissipation reduces to only 0.29W ($I^2 \times R$).

Hence, very low $R_{DS(on)}$ Power MOSFETs can replace the standard rectifiers and the DZDH0401DW controls the MOSFET as an ideal diode.


Critical systems require a fault-tolerant power supply that can be achieved by paralleling two or more PSUs into an (N+1) redundancy configuration.

During normal operation, usually all PSUs equally share the load for maximum reliability. If one of the PSUs is unplugged or fails, then the other PSUs fully support the load. To avoid the faulty PSU from affecting the common bus, an OR'ing rectifier blocks the reverse current flow into the faulty PSU. Likewise during hot-swapping, the OR'ing rectifiers isolate a PSU's discharged output capacitors from the common bus.



Package Outline Dimensions


Please see <http://www.diodes.com/package-outlines.html> for the latest version.



SOT363			
Dim	Min	Max	Typ
A1	0.00	0.10	0.05
A2	0.90	1.00	1.00
b	0.10	0.30	0.25
c	0.10	0.22	0.11
D	1.80	2.20	2.15
E	2.00	2.20	2.10
E1	1.15	1.35	1.30
e	0.650 BSC		
F	0.40	0.45	0.425
L	0.25	0.40	0.30
a	0°	8°	--
All Dimensions in mm			

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.



Dimensions	Value (in mm)
C	0.650
G	1.300
X	0.420
Y	0.600
Y1	2.500

IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com