



SPECIFICATION FOR DYNAMIC ALARM

TOTAL PAGE

06

www.bestargroups.com

RoHS

Specification For The Acoustic Characteristics of dynamic Alarm

Customer		Model Name	BS4515C12V-01
Customer P/N		Product No.	
Date	20 Mar. 18	Issue No.	BS/TEP01.XXXX
Page	01 of 06	Issue Date	18/05/18

Approval:

- 1.Characteristics
- 2.Drawing
- 3.Reliability Test
- 4.Packing
- 5.History change record

Drawn by	Checked by	Approved by	Customer approved

BESTAR HOLDING CO.,LTD

No.199 HuangHe West Road,New district,ChangZhou,JiangSu Province,P.R.China

Tel: +86 519 88222567

Fax: +86 519 88222551

E-mail:wu@be-star.com

<http://www.bestargroups.com>



BS4515C12V-01

1. Characteristics

1.1 Electrical and Mechanical Characteristics

No.	Item	Specifications
1.	Operating Voltage	9-12VDC
2.	Supply Current	<300mA
3.	Sound Pressure Level at 10cm	100±5dB
4.	Resonant Frequency	150-4000Hz
5.	Operating Temperature	-30...+65°C
6.	Storage Temperature	-40...+85°C
7.	Housing Material	ABS777D (Black)
8.	Weight	32g

1.2 Test Method







				Date:	18/05/18	BS4515C12V-01
				Drawn by:	周嘉明	
A	18/05/18	周嘉明		Checked by:	张翔捷	
Rev.	Date	Drawn	Note	Approved by:	王 平	Alarm
BESTAR HOLDING CO.,LTD						DRG NO: BS/TEP01.XXXX
www.bestargroups.com wu@be-star.com						Page:2 of 6

BS4515C12V-01

2. Drawing

Unit:mm Tolerance:±0.3mm



This print and information there in are proprietary to BeStar Holding Co., Ltd.
and shall not be used in whole or in part without its written content

				Date:	18/05/18	BS4515C12V-01	
				Drawn by:	周嘉明		
A	18/05/18	周嘉明		Checked by:	张翔捷	Alarm	
Rev.	Date	Drawn	Note	Approved by:	王 平		
BESTAR HOLDING CO.,LTD						DRG NO: BS/TEP01.XXXX	Page:3 of 6
www.bestargroups.com wu@be-star.com							
6	5	4	3	2	1		

BS4515C12V-01

3. Reliability Test

3.1 high temperature test

Temperature

+65°C

Duration

96hrs

3.2 low temperature test

Temperature

-30°C

Duration

96hrs

3.3 life test in normal temperature

Power supply

12V


Duration

96hrs

3.4 temperature cycle test

Cycles

5



all these tests above should be measured after leaving normal temperature for 2hrs.

3.6 Drop test

Height

70cm

(to 10mm thickness woodenboard)

Direction

3






Notice: All specification must be satisfied in this condition.

This print and information there in are proprietary to BeStar Holding Co., Ltd. and shall not be used in whole or in part without its written content

				Date:	18/05/18	BS4515C12V-01 Alarm
				Drawn by:	周嘉明	
A	18/05/18	周嘉明		Checked by:	张翔捷	
Rev.	Date	Drawn	Note	Approved by:	王 平	
BESTAR HOLDING CO.,LTD						DRG NO: BS/TEP01.XXXX
www.bestargroups.com wu@be-star.com						Page:4 of 6

BS4515C12V-01

4.Packing



Remark:
9 layers per box
20 pcs per layer
9X20x2=360 pcs per box
Size: 58×25×28(cm)

This print and information there in are proprietary to BeStar Holding Co., Ltd. and shall not be used in whole or in part without its written content

				Date:	18/05/18	BS4515C12V-01	
				Drawn by:	周嘉明		
A	18/05/18	周嘉明		Checked by:	张翔捷	Alarm	
Rev.	Date	Drawn	Note	Approved by:	王 平		
BESTAR HOLDING CO.,LTD						DRG NO: BS/TEP01.XXXX	Page:5 of 6
www.bestargroups.com wu@be-star.com							

5. History change record

[illegible]

				Date:	18/05/18	BS4515C12V-01	
				Drawn by:	周嘉明		
A	18/05/18	周嘉明		Checked by:	张翔捷	Alarm	
Rev.	Date	Drawn	Note	Approved by:	王 平		
BESTAR HOLDING CO.,LTD						DRG NO: BS/TEP01.XXXX	Page:6 of 6
www.bestargroups.com wu@be-star.com							