Modular HMI Solutions

Modular Vision 15.6 QCS6490

High end 15.6 inch HMI based on Qualcomm® Dragonwing QCS6490

Flexibility and expandability in a unique modular HMI concept



HIGHLIGHTS

CPU
Qualcomm® Dragonwing QCS6490

CONNECTIVITY
Gb Ethernet, RS485, CAN, RS232, USB, Digital I/O

GRAPHICS
Adreno GPU 643 with support for OpenGL ES 3.2, OpenCL 2.0, Vulkan 1.x, DX FL 12

MEMORY
up to 6 GB LPDDR4-4000 soldered-down memory

Qualcomm

Clea OS

MAIN FIELDS OF APPLICATION

Coffee & Vending | Medical | Industrial Automation | Smart Buildings & Smart Cities | Digital Signage

FEATURES

Processor	1x Arm® Cortex®-A78 @2.7 GHz, 3x Arm® Cortex®-A78 @2.4 GHz, and 4x Arm® Cortex®-A55 @1.8 GHz
Memory	Soldered-down LPDDR5-6400 memory, up to 8 GB total, 32-bit interface 2 channels
Graphics	Qualcomm® AdrenoTM 643L
Video Resolution	15.6" display, resolution 1920 x 1080, LED lifetime 30K hours, 400cd/m² brightness P-Cap (Projected Capacitive touch screen), with 3.0mm chemically strengthened cover glass
Mass Storage	eMMC 5.1 drive soldered on-board, up to 64GB (boot device) SD 4-bit interface (boot device) µSD Card Holder
Networking	1x Gigabit Ethernet interfaces
USB	1x USB C 2.0 Dual Role 1x USB 2.0 Type A
Serial Ports	2x RS-232, 1x RS-485

Other Interfaces	1x I²C, SPI, 2x Digital In, 2x Digital Out 1x speaker out
Power Supply	9 V_{DC} ÷ 32 V_{DC}
Operating System	Clea OS
CAN Bus	1x CAN-FD
Operating Temperature*	0 ÷ 60 °C
Dimensions	407.5 x 259.5 x 52.4 mm

*Measured at any point of SECO standard heatspreader for this product, during any and all times (including start-up). Actual temperature will widely depend on application, enclosure and/or environment. Upon customer to consider application-specific cooling solutions for the final system to keep the heatspreader temperature in the range indicated.


Information subject to change. Please visit www.edge.seco.com to find the latest version of this datasheet

Downloaded from Arrow.com.

Modular Vision 15.6 QCS6490

High end 15.6 inch HMI based on Qualcomm® Dragonwing QCS6490

BLOCK DIAGRAM



Information subject to change. Please visit www.edge.seco.com to find the latest version of this datasheet

034.25

Downloaded from Arrow.com.

Streamline and expedite your edge computing implementations

Clea OS

A flexible operating system that adapts to your needs, thanks to the customization tool and Docker support. Reliability and security are built-in through a dual-partition system and native integration with Exein's robust AI-based protection.

Clea Edgehog


Update, configure, and manage remote devices. Optimize time and costs to maximize operational efficiency and security without the need for costly field interventions.

Clea Astarte

Integrate third-party services, simplify data flows and analysis, and enhance business efficiency by enabling easy and fast utilization of AI.

Clea Portal

Analyze data from remote devices, customize the user experience with applications tailored to user needs, and manage user rights, company access, and tenant privileges.



Scan to know more about our solution

Clea OS

Clea DOCS

Information subject to change. Please visit www.edgeseco.com to find the latest version of this datasheet

Downloaded from Arrow.com.