

MC9S08DZ16ACLF (Active)

S08DZ 8-bit MCU, S08 core, 16KB Flash, 40MHz, QFP 48

- [Data Sheet](#)
- [Product Summary](#)
- [Software & Tools](#)
- [Documentation](#)



Package :
LQFP

plastic, low profile quad; flat
leaded package; 48 terminals;
0.5 mm pitch; 7 mm x 7 mm x 1.4
mm body

Buy Options | Operating Characteristics | Environmental Information | Quality Information | Shipping Information

Operating Characteristics

Parameter	Value
Flash (kB)	16
RAM (kB)	1
EEPROM (kB)	0.512
Core Type	S08
Operating Frequency [Max (MHz)]	20
I ² C	1

Parameter	Value
SPI	1
Supply voltage [min] (V)	2.7
Supply voltage [max] (V)	5.5
GPIO	40
Ambient Operating Temperature (Min-Max) (°C)	-40 to 85
SCI	2

Environmental Information

Material Declaration	PbFree	EU RoHS	Halogen Free	RHF Indicator	2nd Level Interconnect	REACH SVHC	Weight (mg)
MC9S08DZ16ACLF (935317053557)	Yes	Yes Certificate Of Analysis (CoA)	Yes	D	e3	REACH SVHC	178.25

Quality Information

Material Declaration	Safe Assure Functional Safety	Moisture Sensitivity Level (MSL)	Peak Package Body Temperature (PPT) (C°)	Maximum Time at Peak Temperatures (s)
		Lead Free Soldering	Lead Free Soldering	Lead Free Soldering
MC9S08DZ16ACLF (935317053557)	No	3	260	40

Shipping Information

Part Number	Harmonized Tariff (US) Disclaimer	Export Control Classification Number (US)
MC9S08DZ16ACLF (935317053557)	854231	3A991A2

[Investors](#)

[Press, News, Blogs](#)

[Careers](#)

[Mobile Apps](#)

[Contact Us](#)



[NXP Semiconductors Reports Second Quarter 2018 Results](#)

[Read More](#)

[Privacy](#) | [Terms of Use](#) | [Terms of Sale](#) | [Feedback](#)

©2006-2018 NXP Semiconductors. All rights reserved.