

APS5130PD7C-P22
RGB Color Sensor

DESCRIPTION

- The APS5130PD7C-P22 Color Sensor Device, consisting of 3-Channel/1Chip (R, G, B) Si photodiode is a good effective solution to color balance of display backlighting appliances

FEATURES


- Lead-free package
- Component in accordance with RoHS
- SMD style package on PCB technology
- Integral Color Filter in Blue, Green, or Red
- Package: 1500 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- Water clear lens
- RoHS Compliant

APPLICATIONS

The devices are suitable for :


- Colorimetry
- Printing process control
- Display color correction

PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



- Notes:
1. All dimensions are in millimeters (inches).
 2. Tolerance is ±0.25(0.01") unless otherwise noted.
 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 4. The device has a single mounting surface. The device must be mounted according to the specifications.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C (UNLESS OTHERWISE SPECIFIED)

Parameter	Symbol	Value	Unit
Reverse Voltage	V _R	10	V
Operating Temperature	T _{opr}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +85	°C
Soldering Temperature	T _{sd}	260	°C

Note:
1. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.



ELECTRICAL / OPTICAL CHARACTERISTICS at $T_A=25^\circ\text{C}$ (UNLESS OTHERWISE SPECIFIED)

Symbol	Parameter	Condition	Value			Unit
			Min.	Typ.	Max.	
I_{L1}	Light Current (1)	100Lux ^[1] $V_R = 5V$	Red	-	0.039	μA
			Green	-	0.042	
			Blue	-	0.022	
I_{L2}	Light Current (2)	1000Lux ^[1] $V_R = 5V$	Red	-	0.427	μA
			Green	-	0.498	
			Blue	-	0.262	
D	Diameter of the irradiation sensitive area		-	2.0	-	mm
A	Irradiation sensitive area per element		-	0.85	-	mm ²
S_{Max}	Photo sensibility of the single color areas	$\lambda_R = 620\text{ nm}$ $\lambda_G = 550\text{ nm}$ $\lambda_B = 470\text{ nm}$	-	0.33 0.25 0.18	-	A/W
I_D	Reverse Dark Current	$V_R = 5V$	-	-	10	nA
t_r	Rise Time(10% to 90%)	$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 630\text{nm lamp}$	-	5.7	-	μs
		$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 520\text{nm lamp}$	-	5.4	-	
		$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 470\text{nm lamp}$	-	5.4	-	
t_f	Fall Time(90% to 10%)	$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 630\text{nm lamp}$	-	221	-	μs
		$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 520\text{nm lamp}$	-	566	-	
		$R_L = 50\Omega, V_R = 10V, F = 10\text{KHz}, 470\text{nm lamp}$	-	795	-	
$\lambda_{0.1}$	Range of Spectral Bandwidth	Red	570	-	670	nm
		Green	450	-	650	
		Blue	370	-	530	
λ_p	Wavelength of Peak Sensitivity	Red	-	620	-	nm
		Green	-	550	-	
		Blue	-	470	-	

Notes:

1. White fluorescent light (Color Temperature = 6500K) is used as light source.

2. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.



TYPICAL ELECTRO - OPTICAL CHARACTERISTICS CURVES

Fig.4 R,G,B LED Test vs. Output Photocurrent






Fig.5 R,G,B LED Test vs. Output Photocurrent




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes:

1. Don't cause stress to the LEDs while it is exposed to high temperature.
2. The maximum number of reflow soldering passes is 2 times.
3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.



TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)



PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
6. All design applications should refer to Kingbright application notes available at <https://www.KingbrightUSA.com/ApplicationNotes>