




Technical Data

21.08.2023

Shrinkable markers "Ladder Style", thermal transfer
TULT DS – 3:1 Military and Electronics "Ladder Style"

TULT4.8-1.6DS-2x25WH

Article Number 553-71014



Material:

Polyolefin, cross-linked (PO-X)

Colour:

White (WH)

Supplied Ø D min.:

4.8 mm

Recov. Ø d max.:

1.6 mm

Wall (WT):

0.56 mm

Shrink Ratio:

3:1

Min. Shrink Temperature - °C:

+90 °C

Test Method

Flammability:

UL 224 VW-1

Operating Temperature :

-55 °C to +135 °C

Dielectric Strength:

20 kV/mm

ASTM D2671

Longitudinal Change After Shrinkage:

-15% max.

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Technical Data

21.08.2023

Shrinkable markers "Ladder Style", thermal transfer
TULT DS – 3:1 Military and Electronics "Ladder Style"

Print Method:	Thermal transfer print
Print Method (Alternative):	Laser beam print
Application Tool:	H6100, TT431, TT4030, TT4030DS



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved