



Part Number : [1202540114](#)

Product Description : Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Changeover/IOL, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable, 33mm Housing Length

Series Number : 120254

Status : Active

Product Category : Inductive and Photoelectric Sensors

Engineering Number : LTR-M18PA-PMK-603



Documents & Resources

Specifications

[Product Specification 1202540114-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Changeover/IOL, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable, 33mm Housing Length
IP Rating	IP67
Operating Principle	Diffuse
Product Family	Contrinex Inductive and Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068401

Electrical

Polarity	PNP
Switching Frequency	≤ 1500 Hz

Physical

Connection	Cable (PVC 2m, 4-wire)
Length	33mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	3 - 1200mm
Output	Changeover/IOL
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C