

Part Number : 1200878787
Product Description : Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Male (Straight), 24 AWG, WSOR Cable, 0.60m (1.97') Length
Series Number : 120087
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 484031B41M006

Documents and Resources

Drawings

1200878787_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120087
Description	Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Male (Straight), 24 AWG, WSOR Cable, 0.60m (1.97') Length
IP Rating	IP67
Product Name	Micro-Change (M12),Nano-Change (M8)
Type	Double Ended
UPC	889056132527

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.80mm (.189")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Nano-Change (M8)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	43.349/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	24

Downloaded from Arrow.com.