


REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	02/23/17	L.CHAN
B	PER ECN07263	DEC25/17	L.CHAN
C	UPDATE DRAWING	NOV10/17	L.CHAN
D	MODIFY THE LAYOUT	JUL31/18	L.CHAN



FRONT VIEW



SIDE VIEW




RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: ±0.05 (TOP VIEW)

MATERIALS:
PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V–0, COLOR: BLACK.

CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 µ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 µ" [2.54 MICRONS]
MIN. MATTE–TIN OR GOLD FLASH ON CONTACT TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING AT 240°C MAXIMUM FOR 5 SEC MAXIMUM



RECOMMENDED PANEL CUTOUT

PART NUMBER: RJE06–188–0X10

GOLD PLATING:
1 = 6 µ"
2 = 15 µ"
3 = 30 µ"
4 = 50 µ"

AMPHENOL CANADA CORP
RoHS COMPLIANT
2011/65/EU RECAST

UNLESS SPECIFIED OTHERWISE	DRAWN L.CHAN	DATE 02/23/01	Amphenol Canada Corp. Commercial Products
PRIMARY UNITS MILLIMETER	CHECKED J.SI	02/23/01	
SECONDARY INCH	M.E. APP'D		TITLE: RJE06 SERIES, 8 POSITION 8 CONTACT, VERTICAL MOUNT, UNSHIELD WITHOUT FLANGE – RoHS COMPLIANT
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE ±0.38	ENG. REL. NO.		
2 DECIMAL PLACES ±0.25	REF. EAR#: 11306		DWG. NO. P–RJE06–188–0X10 REV D
3 DECIMAL PLACES ±0.20	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1
ANGULAR DEGREES ±1.0°			

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.