Datasheet for part number RMDM-21SCBRM7L61-F222

Our Catalog Part Number: RMDM-21SCBRM7L61-F222
Our Global Manufacturing Part Number: 096515-0963
Brand: Cannon Product Category: Micro Product Line: Micros Series: MICRO

Product Datasheet	
Series	RMDM Micro D
Contact Quantity	21
Contact Gender	Socket
RoHS Compliant	Yes
Shell Style	Receptacle
Contact Material	Gold plated copper alloy
Contact Term Type	PC Tail
Contact Resistance	8 milliohms max.
Termination Type	Right Angle Narrow Profile PCB
Wire Length	0.125" Min, #25AWG
Shell Material	RoHs - Metal Shell
Plating	Nickel
Insulator Material	RoHs - contact size 9 to100 = liquid crystalline polymer, contact arrangements 7C2 or 24C4 = Diallyl phthalate
Hardware	Jackpost, M83513/5-07 - Style
PCB Hardware	No PCB mounting hardware
Coupling	Jackscrew Coupling
Current Rating	3 A max.
Dielectric Withstanding Voltage	600 VAC at sea level 150 VAC at 70,00' altitude
Insulator Resistance	5000 megohms min.
Operating Temperature	-55°C to +200°C
Physical Shock	50 G's, 3 axes, 6 milisecond duration sawtooth pulse
Vibration	20G's, 10-2000 Hz. 12 hours
Durability	500 cycles of mating and unmating, 500 CPH max.
Moisture Resistance	Insulator resistance > 100 megohms
SaltSpray	48 hours

Specifications and dimensions subject to change.

Downloaded from Arrow.com.