

Specifically configured as a Web browser, the Web Panel directly connects to controllers with their own Web servers. The CODESYS 2.3 Web visualization has been specially optimized for the Web Panel.

- Software configuration:**
- Internet browser
  - Java Virtual Machine
  - Panel configuration software

Technical data		
Display diagonal		26.4 cm (10.4 inches)
Display		TFT
Display colors		65536 colors
Graphics resolution		(640 x 480) px
Contrast ratio		500:1
Viewing angle (horizontal/vertical)		-65° ... 65° / -45° ... 65°
Brightness		430 cd/m²
HBT (Half Brightness Time)		50000 h
Visualization		Web-Visu
Communications		Modbus (TCP, UDP) ETHERNET Modbus RTU CANopen
Operating system		Windows CE
Processor		32-bit XScale 520 MHz
Main memory (RAM)		64 MB
Internal memory (flash)		32 MB
Memory		1 MB
Type of memory card		CF card (max. 2 GB)
Transmission rate		ETHERNET: 10/100 Mbit/s
Control Elements		Touch, analog, resistive
Supply voltage		24 VDC (18 ... 30 V)
Input current (max.) (24 V)		500 mA
Operating power		10 W ... 18 W



Connection data		
Connection technology: communication/fieldbus		Modbus (TCP): 1 x RJ-45; Modbus RTU: 1 x D-sub 9 plug; CANopen: 1 x RJ-45; CANopen: 1 x D-sub 9 plug; RS-232 serial interface: 1 x D-sub 9 plug; RS-232 + RS-485/-422 serial interface: 1 x D-sub 9 plug; USB: 2 x USB 2.0 host (type A)

Physical data		
Width		284 mm / 11.181 inches
Height		222 mm / 8.74 inches
Depth		46 mm / 1.811 inches
Panel cutout (W x H)		(268 x 206) mm

Mechanical data		
Mounting type		6 x clamping elements

Material data		
Housing material		Sheet steel, painted
Front panel		Anodized aluminum, natural, polyester film
Fire load		0 MJ
Weight		2100 g
Conformity marking		CE

Environmental requirements		
Ambient temperature (operation)		0 ... +50 °C
Ambient temperature (storage)		-10 ... +60 °C
Protection type		IP65
Note on protection type		IP65 (front side); IP20 (rear side)
Relative humidity (without condensation)		85 %


Commercial data		
Product Group		27 (special components I/O)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454998486
Customs tariff number		84714100000
End of Sale		2021-08-31
End of Production		2021-09-05
End of Delivery		2021-09-15
End of Service and Repair		2023-08-31

Product classification		
UNSPSC		43211903
eCl@ss 10.0		19-20-01-03
eCl@ss 9.0		19-20-04-03
ETIM 9.0		EC001428
ETIM 8.0		EC001428
ECCN		NO US CLASSIFICATION




Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption




Approvals / Certificates


General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-WBP762	EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Downloads




Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 762-1104	

Documentation

Manual				Bid Text			
Product Manual PER- SPECTO® WP, Web Pa- nel	V 1.3.1	pdf 935.59 KB		762-1104	08.05.2015	doc 28.50 KB	
				762-1104	19.02.2019	xml 5.00 KB	

Instruction Leaflet		
Gebrauchs- und Monta- geanleitung	pdf 1542.87 KB	

CAD/CAE-Data

CAD data		CAE data	
2D/3D Models 762-1104		WSCAD Universe 762-1104	
		ZUKEN Portal 762-1104	

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)