

1630 - Protective Equipment Case





Product Image






Dimensions

Outside Dimensions			Inside Dimensions			Drawing
Length	Width	Height	Length	Width	Height	
57.3 in 146 cm	18.5 in 47 cm	8.4 in 21 cm	54.4 in 138 cm	15.4 in 39 cm	6.5 in 16 cm	  
Case Weight						
1630F (with foam)					31.5 lbs	
1630 (w/o foam)					28.0 lbs	

Features

- Meets or exceeds:
 -  **Waterproof - IP67**
 -  **Waterproof - NEMA 4X, 12, 13**
- Automatic pressure equalization system.
- The 1630 case has an interlocking lid that contributes to an overall stronger case.
- Molded-in padlock holes with stainless steel protectors for standard 3/16" shackle TSA approved padlocks (recommended Masterlocks® PN are: 4680D, 4687D, 4688D and Sesamee® PN are: K7470PSB, K6435PSB, K6430PSB)
- Available with latches with keyed chrome **metal locks**.
- Optional multilayer protective cubed **matrix Accuform Foam**
- Available colors:
 -  **Black**
-  **RoHS Compliant**

Customizations

-  **User defined Shapes or Geometry**
-  **Custom Colors**
-  **Metal threaded inserts**
- Keyed locking latches available in **chrome or corrosion proof plastic**
- Optional multilayer protective cubed matrix **Accuform foam**

Certification

For Letter of Certification please [contact us](#).

Accessories

Accuform Foam Sets



Aluminum Panel Kits



Latches with Metal Locks

