




Technical Data

28.03.2022

Shrinkable markers "Ladder Style", thermal transfer
TULT DS – 3:1 Military and Electronics "Ladder Style"

TULT18-6DS-2x25WH

Article Number 553-71038



Material:

Polyolefin, cross-linked (PO-X)

Colour:

White (WH)

Supplied Ø D min.:

18.0 mm

Recov. Ø d max.:

6.0 mm

Wall (WT):

0.90 mm

Shrink Ratio:

3:1

Min. Shrink Temperature - °C:

+90 °C

Test Method

Flammability:

UL 224 VW-1

Operating Temperature - °C:

-55 °C to +135 °C

Dielectric Strength:

20 kV/mm

ASTM D2671

Longitudinal Change After Shrinkage:

-15% max.

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Technical Data

28.03.2022

Shrinkable markers "Ladder Style", thermal transfer
TULT DS – 3:1 Military and Electronics "Ladder Style"

Print Method:

Thermal transfer printing

Application Tool:

H6100, TT431, TT4030, TrakMark DS



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved