



Data Sheet | Item Number: 734-136/108-000

THT male header; 1.0 x 1.0 mm solder pin; straight; 100% protected against mismating;
Threaded flange; Pin spacing 3.5 mm; 6-pole; light gray

<https://www.wago.com/734-136/108-000>



Color: ■ light gray



Dimensions in mm

$L = (\text{pole no.} \times \text{pin spacing}) + 9.5 \text{ mm}$
 $L_1 = (\text{pole no.} \times \text{pin spacing}) + 4.9 \text{ mm}$

Male connector, 734 Series, light gray

This male connector (item number 734-136/108-000) simplifies electrical installations. Dimensions: (30.5 x 14.8 x 8.5) mm (width x height x depth).

The contact surface is coated with tin. THT is used to solder the pcb connector.



Notes	
Safety Information	The MCS – <i>MULTI CONNECTION SYSTEM</i> includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Variants:	Other pole numbers Gold-plated or partially gold-plated contact surfaces Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ .

Electrical data			
Ratings per		IEC/EN 60664-1	
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	160 V	160 V	320 V
Rated impulse withstand voltage	2.5 kV	2.5 kV	2.5 kV
Rated current	10 A	10 A	10 A
Approvals per		UL 1059	
Use group	B	C	D
Rated voltage	300 V	-	300 V
Rated current	10 A	-	10 A
Approvals per		CSA	
Use group	B	C	D
Rated voltage	300 V	-	300 V
Rated current	10 A	-	10 A

Connection Data	
Total number of potentials	6
Number of connection types	1
Number of levels	1
Connection 1	
Pole number	6

Physical data	
Pin spacing	3.5 mm / 0.138 inches
Width	30.5 mm / 1.201 inches
Height	14.8 mm / 0.583 inches
Height from the surface	10.3 mm / 0.406 inches
Depth	8.5 mm / 0.335 inches
Solder pin length	4.5 mm
Solder pin dimensions	1 x 1 mm
Drilled hole diameter	1.4 (+0.1) mm

Mechanical data	
Variable coding	Yes
Anti-rotation protection	Yes

Plug-in connection	
Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	Yes
Mating direction to the PCB	90 °
Locking of plug-in connection	Threaded flange

PCB contact	
PCB contact	THT
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1

Material data	
Note (material data)	Information on material specifications can be found here
Color	light gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E _{Cu})
Contact Plating	Tin
Fire load	0.031 MJ
Weight	2.1 g

Environmental requirements		
Limit temperature range	-60 ... +100 °C	Environmental Testing Test specification: Railway applications – Rolling stock – Electronic equipment DIN EN 50155 (VDE 0115-200):2022-06 Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests DIN EN 61373 (VDE 0115-0106):2011-04 Spectrum/Mounting location Service life test, Category 1, Class A/B Functional test with noise-like oscillations Test passed according to Section 8 of the standard Frequency f₁ = 5 Hz to f₂ = 150 Hz Acceleration 0.101g (highest test level used for all axes) Test duration per axis 10 min. Test directions X, Y and Z axes Monitoring of contact faults and interruptions Passed Voltage drop measurement before and after each axis Passed Simulated service life test through increased levels of noise-like oscillations Test passed according to Section 9 of the standard Frequency f₁ = 5 Hz to f₂ = 150 Hz Acceleration 0.572g (highest test level used for all axes) Test duration per axis 5 h Test directions X, Y and Z axes Extended testing: Monitoring of contact faults and interruptions Passed Extended testing: Voltage drop measurement before and after each axis Passed Shock test Test passed according to Section 10 of the standard Shock pulse form Half sine
Processing temperature	-35 ... +60 °C	



Environmental Testing	
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data	
Product Group	3 (Multi Conn. System)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454618650
Customs tariff number	85366930000

Product Classification	
UNSPSC	39121409
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 10.0	EC002637
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	ef117ec8-6fbe-4baf-99cb-cd4fafd4a949
SCIP notification number (Belgium)	e42cb08a-0628-428a-83b5-6a76d10be370
SCIP notification number (Bulgaria)	82f5fb2b-6b5b-404c-8b53-ea191d0b64f7
SCIP notification number (Czech Republic)	917528fb-85c7-4daf-861a-3d71f79a9a91
SCIP notification number (Denmark)	3626818b-cb90-4483-9472-5dae5783d886
SCIP notification number (Finland)	7507349f-cffc-4d11-a977-8dabec7d8271
SCIP notification number (France)	0eaf0458-8d21-49de-a7d7-6cf42fdbac1c
SCIP notification number (Germany)	936a494d-9675-4c45-9eb9-dc37e5028a1d
SCIP notification number (Hungary)	ac62dd12-75fe-44d7-a1a3-fa5c7664dfe3
SCIP notification number (Italy)	4b5c46c8-f061-4f5d-87ca-62a1c2261719
SCIP notification number (Netherlands)	2b009a62-a9e0-48b6-9f02-2f65d7d3710d
SCIP notification number (Poland)	6be699bc-0808-44c6-93bd-e4c09477e423
SCIP notification number (Romania)	570ed781-393e-474e-9a8a-f8c2c2ec4ba9
SCIP notification number (Sweden)	3370eb64-eef9-4680-a06a-c305714caf2e



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2	1465035
UL Underwriters Laboratories Inc.	UL 1977	E 45171

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready

Approvals for marine applications



Approval	Standard	Certificate Name
BV Bureau Veritas S.A.	IEC 60998	11915/E0 BV

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 734-136/108-000



Documentation

Additional Information
Technical Section 03.04.2019 pdf 2027.26 KB



CAD/CAE-Data

CAD data
2D/3D Models 734-136/108-000



CAE data
ZUKEN Portal 734-136/108-000



PCB Design

Symbol and Footprint via SamacSys 734-136/108-000
Symbol and Footprint via Ultra Librarian 734-136/108-000





1 Compatible Products

1.1 System counterpart

1.1.1 Female connector/socket



Item No.: 734-106/107-000
1-conductor female connector; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 6-pole; 100% protected against mismatching; Screw flange; light gray



Item No.: 2734-106/107-000
1-conductor female connector; push-button; Push-in CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 6-pole; 100% protected against mismatching; Screw flange; light gray

1.2 Optional Accessories

1.2.1 Coding

1.2.1.1 Coding




Item No.: 734-159
Coding key; to be snapped above top level; black



Item No.: 734-130
Coding key; to be snapped above top level; white

Installation Notes

Coding



Coding a male header – fitting coding key(s).