







- ## NOTES



MAGNETIC CHARACTERISTICS		
PARAMETER	PERFORMANCE @ 12 VDC	
	TYPICAL	MAX TOLERANCE
SPAN (-400 TO +400 GAUSS)	6.00 VDC	
NULL (OFFSET AT 0 GAUSS)	6 VDC	±0.6 VDC
SENSITIVITY (MV/GAUSS) (V_0 @ 340g - V_0 @ -340g)/680	9.9	±.3
LINEARITY % OF SPAN		±1.5%
TEMPERATURE ERROR NULL % OF SPAN -40°C TO 150°C -25°C TO 85°C 0°C TO 50°C		±5% ±3% ±2%
GAIN -40°C TO 0°C 0°C TO 150°C	-0.034%/°C -0.077%/°C	

ELECTRICAL CHARACTERISTICS			
	24°C	-40°C TO +150°C	REMARKS
SUPPLY CURRENT (MAX)	16mA	19mA	EXCLUDING LOAD CURRENT 8 TO 16VDC SUPPLY VOLTAGE

ABSOLUTE MAXIMUM RATING	
SUPPLY VOLTAGE	-0.5 TO +18.0 VDC
OUTPUT CURRENT	10 mA MAX
STORAGE TEMPERATURE	-40°C TO 150°C
MAGNETIC FLUX	NO LIMIT, THE CIRCUIT CANNOT BE DAMAGED BY MAGNETIC OVERDRIVE

THIRD ANGLE PROJECTION		
		
SCALE	NONE	
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	$\pm .030$
TWO PLACES	(.00)	$\pm .015$
THREE PLACES	(.000)	$\pm .005$
ANGLES		$\pm$
WEIGHT		



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
MICRO SWITCH a Honeywell Division FED. MFG. CODE 91929	SOLID STATE LINEAR OUTPUT HALL EFFECT TRANSDUCER	CATALOG LISTING
		91SS16-3