

Part Number : [2016061625](#)

Product Description : High Current Universal Clamp Terminal Block, 35.00mm DIN-rail or Screw Mount, 230.0A / 1000V, Grey Housing, Red Cover, 1 Circuit

Series Number : 201606

Status : Active

Product Category : Terminal Blocks and Barrier Strip

Engineering Part Number : MX-KE162.4




Documents and Resources

Drawings

[2016061625_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	201606
Description	High Current Universal Clamp Terminal Block, 35.00mm DIN-rail or Screw Mount, 230.0A / 1000V, Grey Housing, Red Cover, 1 Circuit
Application	Wire-to-Wire
Component Type	One Piece
Keyword	HCUC
Product Name	Universal Clamp
Type	High-Current Universal Clamps
UPC	78172551175

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	230.0A
Voltage - Maximum	1000V

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Gray
Entry Angle	Horizontal
Lock to Mating Part	No
Material - Metal	Aluminum

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide (PA)
Number of Rows	1
Orientation	Vertical
Panel Mount	Screws
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw
Wire Size (AWG)	2(2-6), 4/0-4, 6+6+6
Wire Size mm ²	13.30+13.30+13.30, 2(13.30-33.60), 21.00-107.00

This document was generated on Apr 20, 2026