

Centrifugal fans with forward curved blades

Product news
Product search
Compact fans
Axial fans
Centrifugal fans
RadiCal centrifugal fans
RadiCal DC centrifugal fans
RadiCal with scroll housing
RadiPac centrifugal fans
RadiFit centrifugal fans
Centrifugal fans with forward curved blades
Fans for Fan coil units and air curtains
Forward curved fans with high power density
Tangential fans
Heating technology
Hot air blowers
Pumps
Motors and drive systems
Operating instructions
Ecodesign regulation

Search results list Previous search result Next search result

G4E200-BL03-01

AC centrifugal fan

Motor: M4E074-EI



Technical description	
Weight	7 kg
Motor size	74
Size	200 mm
Rotor surface	Unpainted
Impeller material	Sheet steel, galvanized
Housing material	Sheet steel, galvanized
Direction of rotation	Clockwise, viewed toward rotor
Degree of protection	IP44 / installation- and position-dependent
Insulation class	"F"
Moisture (F) / Environmental (H) protection class	H0 - dry environment
Max. permitted ambient temp. for motor (transport/storage)	+ 80 °C
Min. permitted ambient temp. for motor (transport/storage)	- 40 °C
Installation position	Any
Condensation drainage holes	None
Mode	S1
Motor bearing	Ball bearing
Touch current according to IEC 60990 (measuring circuit Fig. 4, TN system)	< 0,75 mA
Motor protection	Thermal overload protector (TOP) internally connected
with cable	Axial
Protection class	I (with customer connection of protective earth)
Conformity with standards	EN 60335-1
Approval	CCC

Search results list Previous search result Next search result

Further information

You need further information or have a question?

+49 7938 81-0

info1@de.ebmpapst.com

Contact form

ErP Directive

ErP2013 EXCEEDS THE NORM

Downloads

Operating instructions [PDF]

Print

Sitemap

Recommend this page

Bookmark this page

We use cookies to help provide our services. By clicking OK, you agree to allow us to place cookies. Certain services cannot be used without this consent. Learn more

OK

Downloaded from Arrow.com.