

Inductors(Coils) **Inductors(Coils)**

[Product Top Page](#) [Search by Part No.](#) [Search by Characteristics](#) [Cross Reference](#) [Catalog](#) [Tech Notes](#) [Technical Support Tools](#) [Help](#)


**MLF2012A3R3MT000** Inductors(Coils)

**Applications** Commercial Grade

**Feature**  
 Multilayer  
 Magnetic Shield  
 Ferrite Core

**Series** MLF Series / MLF2012 Type

**Status** Production



Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	1.25mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.

Electrical Characteristics	
Inductance	3.3uH +/-20% at 10MHz
Rated Current	50mA
Self-Resonant Frequency [Min.]	60MHz
Self-Resonant Frequency [Typ.]	90MHz
Q [Min.]	45 at 10MHz
Q [Typ.]	70 at 10MHz
DC Resistance [Nom.]	280mΩ
DC Resistance [Max.]	600mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.014g

**Buy Now** (Distributor Inventory Check)

**Contact**








**Documents**

- [Catalog](#)
- [RoHS Certificate](#)
- [REACH Certificate](#)
- [Product Lineup](#)
- [FAQ](#)
- [\[FAQ\] What is a magnetic shield type?](#)

**Design Tools**

- [S-parameter](#)
- [SPICE Netlist\(Simple\)](#)
- [SPICE Netlist\(Precision\)](#)
- [Components Characteristics Viewer](#)

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



**Products**

» [Search by Part No.](#) » [Search by Characteristics](#) » [Distributor Inventory Check](#)

- » Capacitors
- » Inductors (Coils)
- » EMC Components
- » RF / SAW Components and Modules
- » Voltage Protection Devices
- » Current Protection Devices
- » Temperature Protection Devices
- » Sensors and Sensor Systems
- » Ceramic Switching / Heating, Piezo Components and Buzzers
- » Transformers
- » Ferrites and Accessories
- » Noise Suppression Sheets / Magnetic Sheets
- » Anechoic Chambers and Radio Wave Absorbers
- » Power Supplies
- » Magnets
- » Flash Storage
- » Wireless Charging
- » FA Systems
- » ITO Transparent Conductive Film
- » Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

**Application Guides**

- Technical Support**
- Tech Library**
- Environment**
- Contact**
- News**
- Home**

- About TDK
- TDK Worldwide