



E32-T14 2M

Fiber optic sensor head, through-beam, long distance detection, square, side-view, R25 fiber, 2 m cable

Specifications

Sensing method	Through-beam
Shape	Square
Product Width (unpacked)	10.5 mm
Product Depth (unpacked)	8 mm
Product Height (unpacked)	25.2 mm
Application	Long distance detection
Temperature range	-40-70 °C
Sensing distance	4000 mm
Cable length	2 m
Bending radius	25 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Side-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color mark sensor



E3NX-CA

High-performance color mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital fiber amplifier



E3X-NA

Digital fiber amplifier with potentiometer adjustment

Downloads

CAD Library



E32-LT/LD Hex-shaped Fiber Unit Brochure

EN PDF 6.35 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Sensor Selection Selection Guide

EN PDF 16.2 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 26 June, 2025. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://industrial.omron.eu)