






8CKTS

注記 NOTES



- 材質
ウエハー：耐熱性ナイロン UL94V-0
ピン：銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール：銅合金、ニッケル下地、錫メッキ
MATERIAL
WAFER: POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FINNTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色：ナチュラル、黒、赤、青
COLOR: NATURAL, BLACK, RED, BLUE
- 嵌合相手：
ハウジング:502351-**0*
錫メッキ端子:50212-8*00,50372-8*00,560085-0101
金メッキ端子:56161-8*81
MATES WITH
HOUSING:502351-**0*
SN PLATING TERMINAL: 50212-8*00,50372-8*00,560085-0101
AU PLATING TERMINAL: 56161-8*81

- エンボス梱包品の詳細はSD-560020-002参照
DETAILED TAPING PACKAGE, SEE SD-560020-002
- 半田付け面のコプラナリティ: 0.1mm MAX.
CO-PLANARITY OF SOLDER TAILS TO BE 0.1mm MAX.
- 一般公差
GENERAL TOLERANCES
10 UNDER: ± 0.2
10 OVER 30 UNDER: ± 0.25
30 OVER: ± 0.3
ANGULAR: $\pm 1^\circ$

INITIAL REVISION:		
DRWN	SHSHIBATA	2009/02/18
CHECK	HKOMATSU	2009/02/18
APPR	AKANESHIGE	2009/02/18



フィッティングネール
FITTING NAIL



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
		DIMENSION UNITS		SCALE	
$\nabla_A = 0$		mm		5:1	
$\nabla_C = 0$		GENERAL TOLERANCES (UNLESS SPECIFIED)			
$\nabla_P = 0$					
DIVISIONAL SYMBOLS			MM	INCH	
		4 PLACES	±	±	
		3 PLACES	±	±	
		2 PLACES	±	±	
		1 PLACE	±	±	
		0 PLACES	±	±	
		ANGULAR TOL		±	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES
				A3-SIZE	560020

CURRENT REV DESC:			
EC NO: 635305			
DRWN: MUNEMOTO		2020/04/02	
CHK'D: HIJIMA		2020/04/03	
APPR: TOSADA		2020/04/06	
INITIAL REVISION:			
DRWN: DRAWN BY		0099/99/99	
APPR: APPR BY		0099/99/99	

molex			
2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT			
PRODUCT CUSTOMER DRAWING			
DOCUMENT NUMBER		DOC TYPE	DOC PART
SD-560020-001		PSD	001
			K
MATERIAL NUMBER		CUSTOMER	
		GENERAL MARKET	
		SHEET NUMBER	
		1 OF 4	

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-560020-001	PSD	001	K
SHEET NUMBER		1 OF 4	

