






① PLATING:
CONTACT AREA: 0,76 μ m Au MIN. OVER 1,27 μ m Ni MIN.
ACTION PIN : 0,5 μ m SnPb MIN. (NO CONVERSION TO LEADFREE)
REMAINDER : Ni

② MATERIAL; PHOSPHORBRONZE.


③ ROW "r" 12 PLATED THROUGH HOLES FOR LOWERSHIELD.

④ HOLE PATTERN FOR FEMALE CONNECTOR TYPE A WITH
UPPERSHIELD, 110+13 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.

5 MAX. BOARD THICKNESS 3,5 mm.

⑥ PLATING:
CONTACT AREA: 0,76 μ m Au MIN. OVER 1,27 μ m Ni MIN.
ACTION PIN : 0,5 μ m Sn MIN.
REMAINDER : Ni

⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT

FIN. HOLE : 0,55 TO 0,65 mm
OTHER REQUIREMENTS: SEE
APPLICATION SPECIFICATION
114-19029

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KATANO 31MAY04 CHK T.KIMURA 31MAY04 APVD K.IKEGAMI 31MAY04		 Tyco Electronics Kawasaki, Japan Z-PACK 2mm HM GROUND RETURN LOWERSHIELD TYPE A		NAME 名称											
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3				SIZE		CAGE CODE		DRAWING NO 番号		RESTRICTED TO					
		0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ± 3°				PRODUCT SPEC 製品規格 108-19082		APPLICATION SPEC 取付適用規格 114-19029		A2		00779		C-1746790		—	
MATERIAL 材料		FINISH 仕上				WEIGHT —		CUSTOMER DRAWING		SCALE 尺度 5:1		SHEET 1 OF 1		REV B			