


Part Number : [548611770](#)

Product Description : 2.00mm Pitch HIC/LCD Pin Connector, Vertical, Surface Mount, 17 Circuits

Series Number : 54861

Status : Obsolete


Product Category : Sockets



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
--------	----------

Category	Sockets
Series	54861
Description	2.00mm Pitch HIC/LCD Pin Connector, Vertical, Surface Mount, 17 Circuits
Component Type	Socket
Product Name	N/A
UPC	822350750134

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Circuits (Loaded)	17
Circuits (maximum)	17
Color - Resin	Natural
Durability (mating cycles max)	10
Entry Angle	Vertical
Keying to Mating Part	N/A
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	800.600/mg
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.00mm
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

This document was generated on Jul 30, 2024