

AGM-SL 12/200



Product code: 63001851

MASTERVOLT
THE POWER TO BE INDEPENDENT

ONLY AVAILABLE FOR THE US MARKET!

In AGM batteries, the electrolyte (mixture of water and sulphuric acid) is largely absorbed in glass fibre. This type of battery is entirely maintenance-free and there is no gas formation with normal use. Not requiring any ventilation, these batteries can be installed anywhere.

Their construction gives a very fast discharge at very high currents so AGM batteries are ideal for systems that require high currents (for instance when starting an engine). The battery poles can be unscrewed and this type of battery can be combined with every standard battery terminal.

- Ideal universal and very slim battery; suitable for starter functions.
- Compressed AGM technology.
- Saves up to 15 % in volume.
- Saves up to 15 % in weight.
- Miniscule footprint; 2x 200 Ah for a 200 Ah battery footprint.
- Can be combined with every standard battery terminal.
- Two year warranty.

Specifications

General specifications

Nominal battery voltage	12 V
Nominal battery capacity C20	200 Ah
Max. charge current	53 A
Terminals	M6
Max. outer dimensions (incl. terminals/grip handles), lxwxh	560 x 126 x 280 mm 22.0 x 5.0 x 11.0 inch
Weight	51.2 kg 112.9 lb

Technical specifications

CCA to DIN	580 A
CCA to SAE	930 A