

## Han 32A-asg1-K-21



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 0220
Specification	Han 32A-asg1-K-21
HARTING eCatalogue	<a href="https://harting.com/09200320220">https://harting.com/09200320220</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han A®
Type of hood/housing	Surface mounted housing
Description of hood/housing	With thermo-plastic cover
Type	High construction

### Version

Size	32 A
Version	Side entry
Number of cable entries	1
Cable entry	1x Pg 21
Locking type	Double locking lever (on the hood)
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	4
Type rating acc. to UL 50 / UL 50E	4X
	12

### Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------

Page 1 / 2 | Creation date 2025-10-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.  
HARTING Electric Stiftung & Co. KG | Wilhelm-Hartung-Straße 1 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97100 | [electric@HARTING.com](mailto:electric@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

## Commercial data

Packaging size	1
Net weight	440 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140040007
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466