

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

DEC ,2011.

© COPYRIGHT 2011 By --

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

GP

00

P

LTR

DESCRIPTION

DATE

DWN

APVD



F

REVISED PER ECO-18-006244

24APR2018

AP

DG



1. FOR ASSEMBLY DETAILS, REFER TO LEAFLET 2227518-1.

5. 15 POSITION SHOWN.

2. BULK PACKAGED BACKSHELL ASSEMBLIES: ITEMS 1 THRU 4, 100 TIMES QTY SHOWN IN TABLE IN 1 BAG FOR EACH ITEM. ALL BAGS IN 1 BOX WITH (1) 2227518-1 LEAFLET.

6. TRIVALENT CHROMIUM CHROMATE COATING OVER ZINC PLATING.

7. OPTIONAL CABLE CRIMP KIT AVAILABLE FOR 6.0-9.5 DIAMETER CABLE. SEE 1478764.


3. INDIVIDUALLY PACKAGED SHELL ASSEMBLIES: 1 BAG CONTAINS ALL COMPONENTS FOR 1 COMPLETE ASSEMBLY. 100 BAGS PER BOX, (1) 2227518-1 LEAFLET PER BOX.

4. TERMINATES 4.0-13.0 CABLE DIAMETERS.

|           |      |      |      |                                |                  |            |          |             |
|-----------|------|------|------|--------------------------------|------------------|------------|----------|-------------|
| 3         | 63.5 | 52.2 | 69.5 | PHILLIPS                       | 4-40 UNC         | 4          | 37 WAY   | 5-2198617-4 |
| 3         | 47.0 | 47.8 | 53.0 | PHILLIPS                       | 4-40 UNC         | 3          | 25 WAY   | 5-2198617-3 |
| 3         | 33.3 | 40.5 | 39.3 | PHILLIPS                       | 4-40 UNC         | 2          | 15 WAY   | 5-2198617-2 |
| 3         | 25.0 | 38.3 | 31.0 | PHILLIPS                       | 4-40 UNC         | 1          | 9 WAY    | 5-2198617-1 |
| 2         | 63.5 | 52.2 | 69.5 | PHILLIPS                       | 4-40 UNC         | 4          | 37 WAY   | 3-2198617-7 |
| 2         | 47.0 | 47.8 | 53.0 | PHILLIPS                       | 4-40 UNC         | 3          | 25 WAY   | 2-2198617-5 |
| 2         | 33.3 | 40.5 | 39.3 | PHILLIPS                       | 4-40 UNC         | 2          | 15 WAY   | 1-2198617-5 |
| 2         | 25.0 | 38.3 | 31.0 | PHILLIPS                       | 4-40 UNC         | 1          | 9 WAY    | 2198617-9   |
| PACKAGING | C    | B    | A    | SELF TAPPING FIXING SCREW TYPE | JACKSCREW THREAD | SHELL SIZE | POSITION | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.  
DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009

DIMENSIONS:  
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± 0.5  
1 PLC ± 0.5  
2 PLC ± 0.5  
3 PLC ± 0.5  
4 PLC ± 0.5  
ANGLES ± 0.5°  
FINISH

MATERIAL

SEE TABLE

SEE TABLE

DWN 08DEC2011

C. VALENTINE

CHK 08DEC2011

C. ROHDE

APVD 08DEC2011

C. ROHDE

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

**STE** TE Connectivity

NAME

SHIELDED PLASTIC BACKSHELL  
STRAIGHT ENTRY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2198617

SCALE NTS

SHEET

1 OF 1

REV F

|      |                           |                         |        |     |
|------|---------------------------|-------------------------|--------|-----|
| 4    | JACKSCREW ASSEMBLY, 4-40  | POLYAMIDE, UL94 V2 KNOB | BLACK  | 2   |
| 3    | STRAIN RELIEF SET         | POLYCARBONATE UL94 V0   | BLACK  | 1   |
| 2    | SELF TAPPING FIXING SCREW | CARBON STEEL            | 6      | 2   |
| 1    | BACKSHELL HALF            | ABS UL94 V0             | NICKEL | 2   |
| ITEM | DESCRIPTION               | MATERIAL                | FINISH | QTY |