


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior concert, & that no right is granted to disclose or to use any information in this document.

Customer drawing







RECOMMENDED P.C.B LAYOUT
(TOLERANCE +/−0.05)

Amphenol Shenzhen RoHS Compliant 2011/65/EU

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	12/12/08	IP
2	HK--	Update the Drawing	12/31/13	IP

D-SUB TECHNICAL DATA

SHELL :	SPCC, 100u" min tin over 50u" min nickel over 50u'' min copper
BODY :	PBT, UL 94V-0, Color:Black.
CONTACTS :	Copper alloy Gold flash over 50u'' nickel on mating area 100u'' tin over 50u'' nickel on solder area
BRACKET :	Zinc alloy, Nickel plated
BOARDLOCK:	Copper alloy. Tin plated
ELECTRICAL :	Current rating 3A Withstanding Voltage >1000 VAC RMS Insulation resistance >1000 M Ohms Voltage rating 250 VAC (RMS) Max. Contact resistance 25 mOhms max.

PRODUCT CODE

L 17H 1 4 4 0 1 3 4

- L: RoHS Compliance
- Spacing between ports: 1 − F=15.88mm, G=28.43mm
- Top connector: 4 =15Pos. Female
- Bottom connector: 4 =15Pos. Female
- Flange mounting options: 4=M3 Rear Insert
- Board mounting options: 3= Quad Arrowhead Boardlocks
- Shell Plating: 1 = Tin
- Contact Plating: 0 = Flash Gold

UNLESS OTHERWISE SPECIFIED TOLERANCES

	U.S.	METRIC
.X +/-		0.50
.XX +/-		0.30
.XXX +/-		0.20
FRACTIONS +/-		
ANGLES +/-		5°

FOR MATERIALS AND FINISHES SEE NOTES

REMOVE SHARP EDGES

DIMENSIONS U.S. / METRIC — INCHES / MM

APPROVAL		DATE
DRAWN	Felix Liu	12/31/13
CHECKED	Tony.Tang	12/31/13
CHECKED		

DRAWING FILE :

ANGLE OF PROJECTION

Amphenol

Amphenol East Asia Limited

TITLE: D-SUB, Dual port type, L17H Series

SIZE	DRAWING NO.	REV.
A4	C L17H1440134	2

SCALE NONE — SHEET 1 OF 1

Downloaded from Arrow.com.