




REV.	DATE	ECR NO.	DESCRIPTION
A	01/07/99	—	ADD CRIMP NOTES / CHANGE FERRULE DIMS.
B	01/18/06	—	UPDATE DRAWING FORMAT
C	11/20/07	—	REVISE BARREL, CONTACT PIN, FERRULE DIMENSIONS
D	09/17/08	—	ADD FLAT TO BODY/ REVISE FERRULE DIMENSIONS/ ADD NOTE 3 REVISE CABLE DESCRIPTION TO 316/U DB CABLE



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .151" [3.83]
2. CONTACT PIN TO SOLDER.
3. MAX. PANEL THICKNESS OF 3.20 [1.26"]

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8					DRAWN	GRS	09/17/08							
7	HEAT SHRINK TUBING				BLK	A/R	CHECKED			PART DESCRIPTION SMA BULKHEAD CRIMP JACK (FOR 316/U DOUBLE BRAID CABLE)				
6	FERRULE	COPPER	GOLD		1	ISSUED								
5	HEX NUT	BRASS	GOLD		1	SHEET	1 OF 1		PART NO. 132176					
4	LOCK WASHER	BRASS	GOLD		1									
3	CONTACT PIN	BER. COPPER	GOLD		1	CAD FILE		C:/132/132176.DWG		DWG. NO. 132176.DWG REV. NC SIZE A SCALE NA				
2	INSULATOR	PTFE	NATURAL	1										
1	BODY	BRASS	GOLD	1										
DESCRIPTION				MATERIAL	FINISH	QTY								