

Johanson Product Information for 201P45W395KN4

Johanson Company: Johanson Dielectrics inc.

Product Release Date: 10 January, 2006

Deprecated P/N: 201P45W395KN4C-BME

Web Page Link:

<https://www.johansondielectrics.com/switch-mode-ceramic-capacitors>

Datasheet Date: 10-03-2023

Description: Capacitors SMPS P-Series BME - 4 chips, 2324, X7R, 200V, 3.9 μ F $\pm$ 10%, Straight Leads, Packaged in Foam

Size for Capacitors (EIA): 2324

Thickness (Max): 0.545

Life Cycle Stage: Active - Production

Thickness (Min): 0.000

Schedule B: 8532

End Band (Min):

ECCN: EAR99

End Band (Max):

RoHS Compliance: No

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 12

Country of Origin: MX

Product Family: Capacitors

Length (Min): 0.224

Product Subfamily: Capacitors SMPS P-Series BME - 4 chips

Length (Max): 0.275

Capacitance Value: 3.900

Width (Min): 0.000

Cap Unit of Meas: μ F

Width (Max): 0.300

Tolerance: $\pm$ 10%

Packaged Weight (lb) Arm: 0.00

Voltage: 200.0

Packaging: Packaged in Foam

Dielectric Temp Coefficient: X7R

Operating Temp Range: -55°C to +125°C

Termination: 7

Storage Temp Range (Packaged): -65°C to +125°C

Marking: Cap Code & Tol

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%