

NOTES:

1. MATERIALS AND FINISHES:
BODY, BAYONET SLEEVE, WASHER &
RETAINING RING - BRASS, NICKEL PLATING
OUTER CONTACT - BeCu, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
FERRULE - COPPER, NICKEL PLATING
INSULATORS - PTFE, NATURAL
GASKET - FLUOROSILICONE, BLACK
SPRING - STAINLESS STEEL, PASSIVATED
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 18 GHz
C. RETURN LOSS: 30 dB MIN @ DC - 6 GHz
15 dB MIN @ 6 - 12 GHz
D. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
E. INSULATION RESISTANCE: 10,000 MΩ MIN
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65°C TO +165°C


4. ENVIRONMENTAL:
A. THERMAL SHOCK PER MIL-STD-202 METHOD 107
TEST CONDITION B (EXCEPT HIGH TEMP @200°C)
B. VIBRATION: MIL-STD-202 METHOD 204 TEST CONDITION B
C. SHOCK: MIL-STD-202 METHOD 213 TEST CONDITION B
D. CORROSION: MIL-STD-202 METHOD 101
TEST CONDITION B 5% SALT SOLUTION
5. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED:
"AMPHENOL RF, 34-1107-12G DATE CODE"
BAG, OUTER BAG, OR BOX TO BE MARKED:
"U.S. PATENT NO. 7,553,177"
6. HIGH DENSITY INSTALLATION/REMOVAL TOOL: 227-T2000
7. CABLE ASSEMBLY INSTRUCTIONS:
A. TRIM CABLE AS SHOWN.
B. INSERT INSULATOR DISK OVER CENTER CONDUCTOR.
C. CRIMP CONTACT TO CABLE CENTER CONDUCTOR
WITH 0.042" SQUARE DIE
D. CRIMP FERRULE WITH 0.178" HEX.

8 SHOWS CABLE ENTRY DIMENSIONS.



THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	05-Apr-17	03361	RM
B	NOTE 4 IN SHEET 1 WAS CHANGED	07-Aug-18	08804	SH



RECOMMENDED CABLE STRIPPING DIMENSIONS



PROTECTED UNDER U.S. PATENT # 7,553,177

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN W.ZENG	DATE 9-Aug-18	TITLE HD-BNC STR PLUG FOR BELDEN 1855A/4855R CABLE	Amphenol RF www.amphenolrf.com	
	REFERENCE EAR # 7610	ENGINEER K. ELMES	DATE 16-Mar-17		DRAWING NO. 34-1107-12G	
	CONFIGURATION LEVEL: In Work	APPROVED S.HSIEH	DATE 10-Aug-18	SCALE: 5.8:1.0	SHEET 2 OF 2	ITEM NO. 34-1107-12G
	FINISH	CAD FILE		DWG SIZE B	REV B	PART NO. 34-1107-12G