Part Number : 307005207
Product Description : 2.54mm Pitch, H-DAC 64 High Density Automotive Header, Dual Row, Right-Angle, 20 Circuits, Polarization Option 1, Gray, Tray
Series Number : 30700
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

307005207_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-30700-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	30700
Description	2.54mm Pitch, H-DAC 64 High Density Automotive Header, Dual Row, Right-Angle, 20 Circuits, Polarization Option 1, Gray, Tray
Application	Automotive, Wire-to-Board
Comments	Polarization Option 1
Component Type	PCB Header
Product Name	H-DAC 64
UPC	822348101696

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No

Downloaded from Arrow.com.

Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Modified Polystyrene
Net Weight	7.128/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.69mm
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Sealed	Unsealed
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +100°C
Termination Interface Style	Through Hole
Terminal Size	0.635

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number

Downloaded from Arrow.com.

2.54mm Pitch, 0.64mm Width H-DAC 64 High Density Automotive Connectors, Dual Row, Female Harness Assembly, 20 Circuits, Polarization Option 1, Gray	307001207

Downloaded from Arrow.com.