




Wire & Cable > Hook Up Wire > SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire



Cable Type: **MIL-DTL-22759**

Operating Voltage: **600 V**

Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Conductor Material: **Silver-Coated Copper**

Wire Size: **20 AWG**

[All SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire \(235\)](#)

Features

Product Type Features

Cable Style	Primary
-------------	---------

Configuration Features

Number of Strands	19
Number of Conductors	1

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Silver-Coated Copper
Wire Color (Base)	White

Dimensions

	.009 in
Strand Size	32 AWG
Outside Cable Diameter	1.27 mm[.05 in]
Conductor Diameter Range	1.01 mm[.04 in]



Wire Size	20 AWG
-----------	--------

Usage Conditions

Cable Type	MIL-DTL-22759
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]

Other

Product Source	US
----------------	----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # A36675-000
D-200-83

Customers Also Bought

TE Part #806252-000
202C632-51-0

TE Part #CTJ420E016-513
ELEC MODULE

TE Part #CW1922-000
2020D1301-9

TE Part #E57794-000
202G621-780-0

TE Part #814404-000
222D242-4-0

TE Part #ES150-2411V
ES150-2411V=RELAY

TE Part #60824-1
.058 DIA PIN PC PTPPHBZ

TE Part #2-323011-2
TERMINAL,PIDG R SLTD 26-22 6

TE Part #2342834-8
AVC19M FLAT S04 RGB R 500MM/1X6

TE Part #398665-000
TX40AB00-0804

Documents

Product Drawings

22759/43-20-9

English

Datasheets & Catalog Pages

Raychem Wire and Cable Quick Reference Guide

English

Product Specifications

Product Specification



English