

# QUARTZ CRYSTAL MHZ

Part Number: 830026384 | -B | 12SMX

AKA Number: LFX TAL026384




## General Information



Standard 7 x 5mm SMD crystal.

B: 4 pad (metal lid) - A ceramic package with a seam sealed metal lid, hermetically sealed.


## Dimensions [mm]



| Pad | Pad Connection |
|-----|----------------|
| 1   | Crystal        |
| 2   | GND            |
| 3   | Crystal        |
| 4   | GND            |



## Recommended Land Pattern [mm]



## Frequency Parameters

|                       |                         |
|-----------------------|-------------------------|
| Frequency             | 12.0 MHz                |
| Frequency Tolerance   | ± 30 ppm                |
| Frequency Stability   | ± 50 ppm                |
| Operating Temperature | -20 °C to 70 °C         |
| Overtone Order        | Fundamental             |
| Ageing                | ± 5 ppm max. first year |

## Material Parameters

|                                  |                |
|----------------------------------|----------------|
| Termination Finish               | Ni<br>Au       |
| Moisture Sensitivity Level (MSL) | Not Applicable |

## Manufacturing Details

Reflow: 260 °C max over 10 seconds.

## Electrical Parameters

|                         |             |
|-------------------------|-------------|
| Load Capacitance $C_L$  | 16 pF       |
| Shunt Capacitance $C_0$ | 7 pF max.   |
| Drive Level             | 100 µW max. |
| ESR                     | 60 Ω max.   |

## Environmental Parameters

Storage Temperature Range: -40 °C to 125 °C

- Drop Test: In accordance with JIS-C0044; The specimen is measured for its frequency and resistance before the test. It is then dropped from a height of 75 cm or more as a free fall object onto a hard wooden plate of 30 mm or more in thickness.
- Vibration Test: MIL-STD-202 Method 204. 5 g for 20 minutes, 12 cycles in each of the 3 orientations, 10 - 2000 Hz. As per Table 11 of AEC-Q200.

# QUARTZ CRYSTAL MHZ

Part Number: 830026384 | -B | 12SMX

AKA Number: LFX TAL026384



## Company Address

IQD Frequency Products Ltd.  
Station Road  
Crewkerne  
Somerset  
TA18 8AR, United Kingdom

## Technical Standards

|              |                         |
|--------------|-------------------------|
| RoHS Status  | 2015/863/EU - Compliant |
| REACH Status | Compliant               |

## Packaging Details

|                                                                     |                      |
|---------------------------------------------------------------------|----------------------|
| Packaging SPQ                                                       | Tape & Reel 1000 pcs |
| Tape & reel in accordance with EIA-481                              |                      |
| Quantities below the standard reel size to be supplied on cut tape. |                      |