



Product Navigation

[Home](#) [About Us](#) [Products](#) [Investor Relations](#) [News](#) [Contact Us](#) [Secure EAX](#)
Circuit Board Indicators**Panel Mount Indicators****Solid State Lighting****Traffic Signals****Vehicle Lighting****Rail****Obstruction Lighting****Hazardous Area Lighting****Heliport Lighting****how to purchase** [sales contacts](#) [stock check](#) [search](#) [Product Line Search](#)**Please select a Product Line to search.**[Circuit Board Indicators](#) [find](#) [Part # / Text Search](#)**Part No.:** [Text Search:](#) [search](#) [quick links](#)**Dialight Corporate Video**

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF](#)

File**Application Notes**
FAQs**Dialight Ltd (UK)**
Dialight Garufo
Dialight BLP
LumiDrives

menu rendered

Circuit Board Indicators - Through Hole Indicators**P/N# 56402402224F****3 mm Lens Single Color**

Description	3 mm Tri-Level X4 CBI G-G-G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Tri-Level Housing
Configuration	3 mm Lens
Lamp Type	Single Color
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	2mA
Forward Current (mA)	7mA
LED Centerline	2.54
Polarity	Cathode Right

Absolute Maximum Ratings (Ta = 25 °)

Reverse Current	10 @ Vr = 5V
Reverse Voltage	5 V
Solder Temp	260° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



RoHS / pB Free

view PDF

Operating Characteristics

LED Position	1-3
Color	Green
Lamp Type	Single Color
LED Type	Low Current
Intensity Min (mcd)	1
Intensity Typ (mcd)	1.6
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	20
Backlighting	
Pitch Between Vertical	5.08
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Distributor Stock Check

Check stock with our distributors now.

56402402224F

 [check stock](#)