




Automotive Parts > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Material: **Copper Alloy**

Automotive Connector Accessory Type: **Fixation**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Fixation
-------------------------------------	----------

Body Features

Primary Product Material	Copper Alloy
--------------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	4500

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JUNE 2025 (250)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2371101-7 MATENET,INLINE COUPLER ASSY, COD J	TE Part # 2367280-3 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD C	TE Part # 2367280-7 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD J	TE Part # 2367280-9 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD Z
TE Part # 2367280-1 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD A	TE Part # 2367280-2 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD B	 TE Part # 2381609-2 OCEAN-2.0-APPLICATOR-S-203SP173O-SSA	TE Part # 2371101-3 MATENET,INLINE COUPLER ASSY, COD C





TE Part # 2236905-1
NANO TAB 0.5X0.4,TERMINAL



TE Part # 2371101-9
MATENET,INLINE COUPLER ASSY, COD Z



TE Part # 2236905-3
NANO TAB 0.5X0.4,TERMINAL



TE Part # 2381607-2
OCEAN-2.0-APPLICATOR-S-203SP173O-SSA



TE Part # 2302451-1
MATENET, MALE INSERT MODUL




TE Part # 2371101-2
MATENET,INLINE COUPLER ASSY, COD B



TE Part # 2371101-1
MATENET INLINE COUPLER ASSY, COD A



TE Part # 1-1703930-1
NANOMQS, RECEPTACLE TERMINAL



TE Part # 1-1703930-2
NANOMQS, RECEPTACLE TERMINAL



TE Part # 2302450-1
MATENET, FEMALE INSERT MODUL, BLACK

Customers Also Bought



TE Part #2141360-2
HANDHOLD,CRIMP BUSHING



TE Part #2302450-1
MATENET, FEMALE INSERT MODUL, BLACK



TE Part #2302510-1
1-PORT MATENET FRAME,STP, COD A



TE Part #2368022-1
1PORT,GEMNET,SOC HSG ASSY, 180DEG,COD A



TE Part #2368033-1
1PORT,GEMNET,PIN HSG ASSY,COD A,CLPSLT





TE Part #2394145-1
MATENET,INLINE,1P,WITH,CLIP,COD A



TE Part #2421635-1
180deg terminal 1P



TE Part #2405721-1
FEMALE SIGNAL CONTACT



Documents

Product Drawings

MATENET, FIXATION ELEMENT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2302452-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2302452-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2302452-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English