


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	TECHNICAL DATA SHEET RELEASE	12-MAY-14	KMM	RFC



TECHNICAL DATA:

1) MATERIALS:

COUPLING NUT: MACHINED ALUMINUM, ANODIZED
INSULATION INSERT: THERMOPLASTIC, UL 94/V-0
CONTACT: GOLD FLASH PLATING OVER COPPER ALLOY
OVERMOLD MATERIAL: THERMOPLASTIC COLOR: BLACK
CABLE RATING: UL LISTED DUAL RATED TC-ER/STOOW,
CSA TYPE STOOW, FT4 FLAME RATING, 600V,
90°C DRY & 75°C WET (TC-ER), 105°C (STOOW)
CABLE JACKET MATERIAL: PVC COLOR: BLACK
CONDUCTOR INSULATION: PVC
NUMBER OF CONDUCTORS: (4) 10AWG

2) ELECTRICAL DATA:


CURRENT (MAX): 25A
VOLTAGE (MAX): 600V AC/DC
INSULATION RESISTANCE (MIN): 5000M OHMS
DIELECTRIC TEST VOLTAGE: 2200V
SHORT CIRCUIT AMPERAGE RATING: 65kA - BREAKERS AND FUSES

3) MECHANICAL DATA:

TEMPERATURE RANGE: -40°C TO 90°C
PROTECTION: IP67 (MATED CONDITION)
MATING CYCLES: >500
VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204
THERMAL SHOCK PER MIL-STD-202 METHOD 207
48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101

4) RoHS COMPLIANT

5) UL 2237 LISTED ASSEMBLY UL FILE NUMBERS: E339703



Amphenol P/N	ROCKWELL P/N	MOLEX	TURCK
P28976-M*	280-PWRM35A-M*	CC4030A48M*	GSDAGKDA40-*M
P28976-M1	280-PWRM35A-M010	CC4030A48M010	GSDAGKDA40-010M
P28976-M2	280-PWRM35A-M020	CC4030A48M020	GSDAGKDA40-020M
P28976-M3	280-PWRM35A-M030	CC4030A48M030	GSDAGKDA40-030M
P28976-M5	280-PWRM35A-M050	CC4030A48M050	GSDAGKDA40-050M
P28976-M10	280-PWRM35A-M100	CC4030A48M100	GSDAGKDA40-100M

TOLERANCE	
0-2.99 M = +100.0/-25.0mm	0-9.99 FT = +4" / -1"
3-8.99 M = +150.0/-25.0mm	10.00-29.99 FT = +6" / -1"
9-14.99 M = +300.0/-25.0mm	30.00-49.99 FT = +12" / -1"
15-OVER M = +450.0/-25.0mm	50 FT-OVER = +18" / -1"

PART NUMBER		DESCRIPTION		ITEM
QUANTITY		MATERIALS LIST		
UNLESS OTHERWISE SPECIFIED		SIGNATURES		
1) All dimensions are in metric(mm).		DRAWN: KMM 12-MAY-14		
2) Tolerances are as follows:		CHECKED: MRF 12-MAY-14		
1 PL DEC ±0.30 1 Fractions ±1/64		ENGINEER: KMM		
2 PL DEC ±0.15		APPROVAL: RFC 12-MAY-14		
3) Note reference =		CUSTOMER:		
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
PROCESS SPECIFICATIONS:		SIZE	TYPE	DWG NO.
NEXT ASSY:		C-	P28976-Mxxx	A1
		SCALE	FULL	C-P28976
		SHEET	1	OF 1

TM-435 PB LITE, 4 PIN, M/F, 10AWG, TC-ER/STOOW, PVC DWG NO: C-P28976-Mxxx

REV: A1
Sht: 1
OF: 1