Pushing Performance
Since 1945

DIN-Signal harbus64,C,F,PL2-single



Image is for illustration purposes only. Please refer to product description.

Part number	02 05 000 2513
Specification	DIN-Signal harbus64,C,F,PL2-single
HARTING eCatalogue	https://harting.com/02050002513

Identification

Category	Contacts
Series	har-bus® 64
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female contact
Manufacturing process	Stamped contacts
Details	Attention: Single contacts are only recommended for repair and maintenance. For series production we recommend the identical contacts on reel.
Pack contents	Single contact

Technical characteristics

Conductor cross-section (mm²)	0.09 ... 0.5 mm²
Conductor cross-section (AWG)	AWG 28 ... AWG 20
Wire outer diameter	0.7 ... 1.5 mm
Rated current	≤1.5 A
Contact resistance	≤20 mΩ
Stripping length	3.5 ... 4 mm
Performance level	2 acc. to IEC 61076-4-113
Mating cycles	≥250

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Ni Termination side
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
PFAS	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 61076-4-113 (complementary)

Commercial data

Packaging size	1,000
Net weight	0.14 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140000414
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522


HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.


Pushing Performance
Since 1945

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.
Measuring and testing techniques acc. to IEC 60512-5-2



Installation of crimp contacts



Fitting the crimp contacts:
After crimping the wires onto the contacts with the help of a crimping tool or an automatic crimping machine the contacts should be correctly oriented and inserted into the cavities of the connector moulding in the required configuration. They snap into position and are firmly held in place. A light pull on the wire assures the correct tensile strength of the contact. When using stranded wires with a gauge below 0.37 mm^2 an insertion tool is necessary.Insertion tool part number: 09 99 000 0100
Insertion tool part number: 09 99 000 0100
Removing the crimp contacts:
The removal tool is inserted into a slot on the side of the respective crimp cavity. This action compresses the contact retaining spring therefore the contact can then be easily withdrawn using a light pull on the wire. This action will cause no damange to the contact / wire which can be repositioned / refitted as necessary. The drawing demonstrates the crimp removal procedure (max. 5x).
Removal tool part number: 09 99 000 0101

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.