



**Part Number :** [1200668887](#)  
**Product Description :** Micro-Change (M12)  
Double-Ended Cordset with Knurled Hexnut,  
8 Poles, Male (Straight) to Female (90°), 24  
AWG, Black TPU WSOR Cable, 5.0m (16.40')  
Length  
**Series Number :** 120066  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 888031B41M050



Documents & Resources

**Drawings**  
[1200668887\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 8 Poles, Male (Straight) to Female (90°), 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	889056004374

### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

### Physical

Cable Diameter	6.40mm (.252")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass

Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	312.700/g
Orientation	90° to Straight
Poles	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

---

This document was generated on Apr 20, 2025