



NOTES:

1. MATERIALS AND FINISHES:
BODY, CLAMP NUT, WASHERS, BRAID CLAMP,
SHELL, RETAINING RING - BRASS, NICKEL PLATING
CONTACT - BRASS , SILVER PLATING
CONTACT - BeCu, SILVER PLATING
SPRING - BeCu, NICKEL PLATING
INSULATORS - PTFE , NATURAL
GASKETS - SILICONE RUBBER, RED
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 4 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 31-2226, AND DATE CODE"
5. CONTACT PIN TO SOLDER.
- 6> SHOWS CABLE ENTRY DIMENSIONS.



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ± 0.3mm ANGLES ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp.. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp.. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN	DATE	TITLE		Amphenol RF www.amphenolrf.com	
	SEE NOTES	A ARUN PRABU	15-Apr-14				
	REFERENCE	ENGINEER	DATE	SPECIAL PLUG (TWIN CONTACT) BNC LOW VOLTAGE FOR RG-108A CABLE		DRAWING NO. 31-2226	
	EAR #	C.WANG	21-Dec-09			ITEM NO. 31-2226	
	CONFIGURATION LEVEL: □□□□	APPROVED	DATE	SCALE: 4.3:1.0	SHEET 2 OF 2	PART NO. 31-2226	
	FINISH	S.HSIEH	22-Jul-14	DWG SIZE	REV		
		CAD FILE		B	AA		