

Product data sheet

Specifications



APC SERVICE BYPASS PDU, 120V 30AMP W/ (4) NEMA 5-20R AND (1) L5-30R

SBP3000RM

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Product or component type	Bypass kit
Main Output Voltage	120 V
Input Connection Type	NEMA L5-30P
Number of rack unit	2U
Cable length	2.4 m
Number of cables	1
Provided equipment	User manual Rack mounting brackets
Range of product	Maintenance Bypass Panels

Physical

Colour	Black
Height	89 mm
Width	432 mm
Depth	76 mm
Net weight	4.45 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
Permissible voltage	100...125 V
Max line current	30 A
Input current limits	30 A
Load capacity	3000 VA
Power factor	0...1

Output

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Max current draw	30 A
Number of power socket outlets	4 NEMA L5-20R 1 NEMA L5-30R
Number of power socket outlets	5
Protection type	Circuit breaker
Power cable length	1.2 m
Efficiency	99 %

Conformance

Product certifications	TÜV
------------------------	-----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.1 cm
Package 1 Width	29.5 cm
Package 1 Length	46.3 cm
Package 1 Weight	5.27 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained](#) >

[How we assess product sustainability](#) >

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

