




1-521120-3 Product Details

[Share](#) [Print](#) [Email](#)


✓ **Active**

[View 3D PDF](#)

Positive Lock Connectors

HSG RECPT POSILOK MK III 250 V0 NAT

1-521120-3

TE Internal Number: 1-521120-3

Product Highlights [View All](#)

- Connector
- Not Preloaded
- Connector Style = Plug
- 1 Positions
- Accepts Contact Gender = Receptacle

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

[Feedback](#)

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type ?	Connector
Receptacle Style ?	Straight
Keyed ?	No
Color ?	Natural
Profile	Standard

Dimensions

Mating Area Interface Dimensions (mm [in]) ?	6.35 [.250]
--	-------------

Body Features

Position Keyed ?	None
Material ?	Nylon 6/6

Contact Features

Accepts Contact Gender	Receptacle
------------------------	------------

Housing Features

Connector Style	Plug
-----------------	------

Configuration Features

Preloaded	No
Number of Positions	1

Industry Standards

RoHS/ELV Compliance ?	ELV compliant, RoHS compliant
Lead Free Solder Processes ?	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method ?	Loose Piece
--------------------	-------------

Other

Line ?	AMP POSITIVE LOCK Mark III
Brand	AMP

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

