


REV. 0

DCO 142515

TOL ± .010 UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C

RESISTANCE 1350 OHMS ±10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.5 VDC

MUST RELEASE 8.1 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX.

RELEASE 6 MS MAX.

CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 2 AMPS 28 VDC RESISTIVE 50,000 OPERATIONS

DR. PBB 11/27/00 CK. TLG 11-27-00

CII Technologies™ advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/37-022P REV.

"3SBC" RELAY

3SBC2092A2

SUPERSEDED
NOT the LATEST
REVISION

= 7/8 REV D

Downloaded from Arrow.com.