



- ?

[Circuit Board Indicators](#)
- ?

[Panel Mount Indicators](#)
- ?

[Solid State Lighting](#)
- ?

[Traffic Signals](#)
- ?

[Vehicle Lighting](#)
- ?

[Rail](#)
- ?

[Obstruction Lighting](#)
- ?

[Hazardous Area Lighting](#)
- ?

[Heliport Lighting](#)

Region:

Product Line:

Circuit Board Indicators

Check stock with our distributors now.

5977711307F

Please note that the stock check**is only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.

Please select a Product Line to search.

Circuit Board Indicators

Part No.:

Text Search:

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.
[View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)

menu rendered

Circuit Board Indicators - Surface Mount Indicators	
P/N#	1210 Package Tri - Color
5977711307F	
Description	

Solder Temp
Operating Temp
Storage Temp

260Â° for 10 sec
-55~+100° C
-55~+100° C



Distributor Stock Check

Check stock with our distributors now.

5977711307F

Operating Characteristics	
LED Position	
Color	Blue / Green / Red
Lamp Type	Tri -Color / Tri -Color / Tri -Color
LED Type	AllInGaP / InGaN / InGaN
Intensity Min (mcd)	25.0 / 99.0 / 40.0
Intensity Typ (mcd)	40.0 / 160.0 / 80.0
Intensity Max (mcd)	60 / 180 /
Fwd Voltage Min	3.4 / 3.4 /
Fwd Voltage Typ	1.4
Fwd Voltage Max	4.0 / 4.0 /
Dom Wavelength Min (nm)	2.4
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	470 / 525 / 626
Power Dissipation Max (mW)	72 / 120 / 120
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	