

SEK-19 SV HT MA STD STR29 RLG 60P PL2



Image is for illustration purposes only. Please refer to product description.

Part number	09 19 560 6904
Specification	SEK-19 SV HT MA STD STR29 RLG 60P PL2
HARTING eCatalogue	https://harting.com/09195606904

Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight

Version

Termination method	Reflow soldering termination (THR)
Connection type	PCB to cable
Number of contacts	60
Termination length	2.9 mm
Locking type	With long levers

Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	>10 ⁹ Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 60 s)
Insertion force	≤120 N
Withdrawal force	≤120 N
Performance level	2 acc. to IEC 60603-13

Technical characteristics

Mating cycles	≥250
Test voltage U _{r.m.s.}	1 kV
Isolation group	II (400 ≤ CTI < 600)

Material properties

Material (insert)	Thermoplastic resin (PCT)
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	50
Net weight	12.38 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140213470
eCl@ss	27460201 PCB connector (board connector)

Commercial data

ETIM	EC002637
UNSPSC 24.0	39121415

Cross section of solder termination

